


QTTCBS 1,5-PE - Protective conductor double-level terminal block



3050248

<https://www.phoenixcontact.com/us/products/3050248>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective conductor double-level terminal block, 1 level, connection method: Quick connection, cross section: 0.25 mm² - 1.5 mm², connection method: Spring-cage connection, cross section: 0.08 mm² - 4 mm², mounting: NS 35/7,5, NS 35/15, color: green-yellow

Your advantages

- Same shape and pitch as the feed-through terminal blocks
- Contact is made free from mechanical and electrical errors by simply snapping onto the DIN rail
- All the requirements of standard IEC 60947-7-2 are met

Commercial data

Item number	3050248
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE03
Product key	BE3129
GTIN	4017918975890
Weight per piece (including packing)	18.599 g
Weight per piece (excluding packing)	18.599 g
Customs tariff number	85369010
Country of origin	PL

QTTCBS 1,5-PE - Protective conductor double-level terminal block



3050248

<https://www.phoenixcontact.com/us/products/3050248>

Technical data

Product properties

Product type	Ground terminal block
Number of connections	4
Number of rows	2

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	0.56 W

Connection data

Grounding foot	Yes
Number of connections per level	2
Frequency of connections with the same cross section	100
Nominal cross section	1.5 mm ²

1 level

Connection method	Quick connection
Note	Please observe the current carrying capacity of the DIN rails.
Stripping length	10 mm
Material wire insulation	PVC / PE
Connection in acc. with standard	IEC 60947-7-2
Conductor cross-section rigid	0.25 mm ² ... 1.5 mm ²
Cross section AWG	24 ... 16 (converted acc. to IEC)
Conductor cross-section flexible	0.25 mm ² ... 1.5 mm ²
Conductor cross-section, flexible [AWG]	24 ... 16 (converted acc. to IEC)
Flexible conductor cross-section (ferrule with plastic sleeve)	0.25 mm ² ... 1.5 mm ²
Cross section, sensor conductors	0.25 mm ² ... 0.34 mm ²

Level 1+2 above 1

Connection method	Spring-cage connection
Internal cylindrical gage	A3
Connection in acc. with standard	IEC 60947-7-2
Conductor cross-section rigid	0.08 mm ² ... 4 mm ²
Cross section AWG	28 ... 12 (converted acc. to IEC)
Conductor cross-section flexible	0.08 mm ² ... 2.5 mm ²
Conductor cross-section flexible (ferrule without plastic sleeve)	0.14 mm ² ... 2.5 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.14 mm ² ... 2.5 mm ²

QTTCBS 1,5-PE - Protective conductor double-level terminal block



3050248

<https://www.phoenixcontact.com/us/products/3050248>

2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm ²
---	---------------------

Dimensions

Width	5.2 mm
End cover width	2.2 mm

Material specifications

Color	green-yellow
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Cable/line

Wire diameter incl. insulation	3 mm
--------------------------------	------

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-2
----------------------------------	---------------

QTTCBS 1,5-PE - Protective conductor double-level terminal block



3050248

<https://www.phoenixcontact.com/us/products/3050248>

	IEC 60947-7-2
--	---------------

Mounting

Mounting type	NS 35/7,5
	NS 35/15


QTTCBS 1,5-PE - Protective conductor double-level terminal block

3050248

<https://www.phoenixcontact.com/us/products/3050248>

Drawings

Circuit diagram



QTTCBS 1,5-PE - Protective conductor double-level terminal block



3050248

<https://www.phoenixcontact.com/us/products/3050248>

Classifications

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

QTTCBS 1,5-PE - Protective conductor double-level terminal block



3050248

<https://www.phoenixcontact.com/us/products/3050248>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com