

AKG 16 YE - Connection terminal block



3062977

<https://www.phoenixcontact.com/us/products/3062977>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connection terminal block, nom. voltage: 300 V, nominal current: 76 A, connection method: Screw connection, Rated cross section: 16 mm², cross section: 1.5 mm² - 16 mm², mounting: Neutral busbar, color: yellow

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3062977 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Product key | BE7331 |
| GTIN | 4046356558372 |
| Weight per piece (including packing) | 10.536 g |
| Weight per piece (excluding packing) | 10.426 g |
| Country of origin | DE |

AKG 16 YE - Connection terminal block



3062977

<https://www.phoenixcontact.com/us/products/3062977>

Technical data

Product properties

| | |
|-----------------------|-----------------------------|
| Product type | Installation terminal block |
| Number of connections | 1 |
| Number of rows | 1 |

Electrical properties

| | |
|---|--|
| Maximum load current | 76 A (with 16 mm ² conductor cross-section) |
| Maximum power dissipation for nominal condition | 2.43 W |
| Nominal current I _N | 76 A |
| Current carrying capacity of the neutral busbar | 140 A |

Connection data

| | |
|-----------------------|--|
| Nominal cross section | 16 mm ² |
| Maximum load current | 76 A (with 16 mm ² conductor cross-section) |

Level 1 above 1 below 1

| | |
|---|--|
| Connection method | Screw connection |
| Screw thread | M5 |
| Tightening torque | 2.5 ... 3 Nm |
| Stripping length | 16 mm |
| Conductor cross-section rigid | 1.5 mm ² ... 16 mm ² |
| Cross section AWG | 14 ... 6 (converted acc. to IEC) |
| Conductor cross-section flexible | 1.5 mm ² ... 16 mm ² |
| Conductor cross-section, flexible [AWG] | 14 ... 6 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 1.5 mm ² ... 16 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 1.5 mm ² ... 16 mm ² |
| 2 conductors with same cross section, rigid | 1.5 mm ² ... 6 mm ² |
| 2 conductors with same cross section, flexible | 1.5 mm ² ... 6 mm ² |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve | 1.5 mm ² ... 6 mm ² |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 1.5 mm ² ... 10 mm ² |
| Nominal cross section | 16 mm ² |
| Nominal current | 76 A |
| Maximum load current | 76 A (with 16 mm ² conductor cross-section) |
| Nominal voltage | 300 V |

Dimensions

| | |
|--------|---------|
| Width | 9.8 mm |
| Height | 23.7 mm |
| Depth | 29 mm |
| Length | 23.7 mm |

AKG 16 YE - Connection terminal block



3062977

<https://www.phoenixcontact.com/us/products/3062977>

Material specifications

| | |
|--|-------------------|
| Color | yellow (RAL 1018) |
| Flammability rating according to UL 94 | V2 |
| Insulating material | PA |

Environmental and real-life conditions

Ambient conditions

| | |
|--|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Mounting

| | |
|---------------|----------------|
| Mounting type | Neutral busbar |
|---------------|----------------|

AKG 16 YE - Connection terminal block





3062977


<https://www.phoenixcontact.com/us/products/3062977>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3062977>

|  CSA Approval ID: 13631 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | - | 65 A | 18 - 6 | - |

|  UL Recognized Approval ID: E60425 | | | | |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| B | | | | |
| | - | 65 A | 18 - 6 | - |
| C | | | | |
| | - | 65 A | 18 - 6 | - |
| F | | | | |
| | - | 65 A | 18 - 6 | - |

|  EAC Approval ID: KZ7500651131219505 | | | | |
|---|--|--|--|--|
|---|--|--|--|--|

AKG 16 YE - Connection terminal block



3062977

<https://www.phoenixcontact.com/us/products/3062977>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250116 |
| ECLASS-15.0 | 27250116 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000001 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31162900 |
|-------------|----------|

AKG 16 YE - Connection terminal block



3062977

<https://www.phoenixcontact.com/us/products/3062977>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com