

FTP-2/1 SERVICE 0R1 - Test plug



3069466

<https://www.phoenixcontact.com/us/products/3069466>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Test plug, with integrated resistance of 100 mOhm, 3 W, nom. voltage: 400 V, nominal current: 1 A, Rated cross section: 2.5 mm², color: red

Your advantages

- Easy and time saving, thanks to functional grouping of switching operations
- Cost-effective, thanks to the tailored, modular design and use of standardized CLIPLINE complete accessories
- Maximum safety with leading and automatic transformer short circuit
- The integrated, robust switch contact is designed for the most stringent demands, and the use of high-quality materials ensures the transmission of signal currents, even after multiple actuations

Commercial data

Item number	3069466
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BE6112
GTIN	4055626345949
Weight per piece (including packing)	65.3 g
Weight per piece (excluding packing)	65.3 g
Country of origin	PL

Technical data

Product properties

Product type	Test plug terminal block
Product family	FAME 2
Number of positions	1
Pitch	8.2 mm
Number of connections	2
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
----------------------	-----

Electrical properties

Rated surge voltage	4 kV
Maximum power dissipation for nominal condition	1.31 W
Test surge voltage	5 kV

Connection data

Nominal cross section	6 mm ²
Test socket torque	0.5
Note	The conductor cross-section depends on the cable lug used
Conductor cross-section flexible	0.5 mm ² ... 2.5 mm ²
Conductor cross-section, flexible [AWG]	20 ... 14 (converted acc. to IEC)
Nominal cross section	2.5 mm ²
Nominal current	1 A
Maximum load current	4 A (at 20°C ambient temperature, max. 6 minute load and min. 12 minute pause)
Nominal voltage	400 V AC/DC

Dimensions

Width	9 mm
Height	86 mm
Pitch	8.2 mm

Material specifications

Color	red (RAL 3001)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA

Mechanical properties

Mechanical data

FTP-2/1 SERVICE 0R1 - Test plug



3069466

<https://www.phoenixcontact.com/us/products/3069466>

Open side panel	No
-----------------	----

Environmental and real-life conditions

Ambient conditions


Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	Insertion in base strip
---------------	-------------------------

Drawings

Circuit diagram



FTP-2/1 SERVICE 0R1 - Test plug



3069466

<https://www.phoenixcontact.com/us/products/3069466>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3069466>



EAC

Approval ID: KZ7500651131219505

FTP-2/1 SERVICE 0R1 - Test plug



3069466

<https://www.phoenixcontact.com/us/products/3069466>

Classifications

ECLASS

ECLASS-13.0	27250304
ECLASS-15.0	27250304

ETIM

ETIM 10.0	EC002555
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FTP-2/1 SERVICE 0R1 - Test plug



3069466

<https://www.phoenixcontact.com/us/products/3069466>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com