

STG 2-VBST 4 - Connector housing



3070422

<https://www.phoenixcontact.com/us/products/3070422>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector housing, depth: 45 mm, width: 12.1 mm, height: 15.7 mm, number of positions: 2, color: black

Commercial data

Item number	3070422
Packing unit	1,500 pc
Minimum order quantity	1,500 pc
Sales key	BE29
Product key	BE5Z3X
GTIN	4046356559560
Weight per piece (including packing)	2.405 g
Weight per piece (excluding packing)	2 g
Customs tariff number	85389099
Country of origin	DE

STG 2-VBST 4 - Connector housing



3070422

<https://www.phoenixcontact.com/us/products/3070422>

Technical data

Product properties

Product type	Mounting material
Number of positions	2

Dimensions

Width	12.1 mm
Height	15.7 mm
Depth	45 mm

Material specifications

Color	black (RAL 9005)
Material	PA
Flammability rating according to UL 94	V0

STG 2-VBST 4 - Connector housing



3070422

<https://www.phoenixcontact.com/us/products/3070422>

Classifications

ECLASS

ECLASS-13.0	27440202
ECLASS-15.0	27440202

ETIM

ETIM 10.0	EC000437
-----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

STG 2-VBST 4 - Connector housing



3070422

<https://www.phoenixcontact.com/us/products/3070422>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.022 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com