

# PP-H 1,5/S/1-R - Plug



3212714

<https://www.phoenixcontact.com/us/products/3212714>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug, nom. voltage: 500 V, nominal current: 17.5 A, number of connections: 1, number of positions: 1, connection method: Push-in connection, Rated cross section: 1.5 mm<sup>2</sup>, 1 level, cross section: 0.14 mm<sup>2</sup> - 1.5 mm<sup>2</sup>, color: gray

## Product description

Connector element right, left housing with engagement pin, right closed with cover

## Your advantages

- Large-surface labeling option
- The Push-in technology COMBI plugs for self-assembly provide solutions that users can implement themselves
- Tested for railway applications

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3212714       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE22          |
| Product key                          | BE2244        |
| GTIN                                 | 4046356565851 |
| Weight per piece (including packing) | 2.08 g        |
| Weight per piece (excluding packing) | 2.016 g       |
| Customs tariff number                | 85366990      |
| Country of origin                    | PL            |

# PP-H 1,5/S/1-R - Plug



3212714

<https://www.phoenixcontact.com/us/products/3212714>

## Technical data

### Notes

|                    |   |
|--------------------|---|
| Notes on operation | COMBI connectors are connectors without switching power in accordance with IEC 61984 and can be connected or disconnected without load or voltage when used as intended |
|--------------------|---|

### Product properties

|                       |                   |
|-----------------------|-------------------|
| Product type          | Terminal plug     |
| Area of application   | Railway industry  |
|                       | Machine building  |
|                       | Plant engineering |
| Number of positions   | 1                 |
| Pitch                 | 3.5 mm            |
| Number of connections | 1                 |
| Number of rows        | 1                 |
| Potentials            | 1                 |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|   |        |
|---|--------|
| Rated surge voltage                             | 6 kV   |
| Maximum power dissipation for nominal condition | 0.56 W |

### Connection data

|                                 |                     |
|---------------------------------|---------------------|
| Number of connections per level | 1                   |
| Nominal cross section           | 1.5 mm <sup>2</sup> |

#### 1 level

|   |   |
|---|---|
| Connection method   | Push-in connection  |
| Stripping length  | 8 mm ... 10 mm  |
| Internal cylindrical gage   | A1 / B1   |
| Connection in acc. with standard                                  | IEC 61984   |
| Conductor cross-section rigid                                     | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>              |
| Cross section AWG   | 26 ... 16 (converted acc. to IEC)                         |
| Conductor cross-section flexible                                  | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>              |
| Conductor cross-section, flexible [AWG]                           | 26 ... 16 (converted acc. to IEC)                         |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>              |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 0.14 mm <sup>2</sup> ... 1 mm <sup>2</sup>                |
| Nominal cross section   | 1.5 mm <sup>2</sup>                                       |
| Nominal current   | 17.5 A (observe derating)                                 |
| Maximum load current  | 17.5 A (with 1.5 mm <sup>2</sup> conductor cross-section) |
| Nominal voltage   | 500 V   |

# PP-H 1,5/S/1-R - Plug



3212714

<https://www.phoenixcontact.com/us/products/3212714>

1 level Connection cross sections directly pluggable

|   |  |
|---|--|
| Conductor cross-section rigid                                     | 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.34 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 0.34 mm <sup>2</sup> ... 1 mm <sup>2</sup>   |

## Dimensions

|        |         |
|--------|---------|
| Width  | 3.5 mm  |
| Height | 16.5 mm |
| Depth  | 31.3 mm |
| Pitch  | 3.5 mm  |

## Material specifications

|   |                 |
|---|-----------------|
| Color   | gray (RAL 7042) |
| Flammability rating according to UL 94                                  | V0              |
| Insulating material group   | I               |
| Insulating material   | PA              |
| Static insulating material application in cold                          | -60 °C          |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C          |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3     |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 28 MJ/kg        |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed          |

## Mechanical properties

Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Environmental and real-life conditions

Ambient conditions

|  |   |
|--|---|
| Ambient temperature (operation)          | -60 °C (max. operating temperature see derating curve)                    |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C   |
| Ambient temperature (actuation)          | -5 °C ... 70 °C   |
| Permissible humidity (operation)         | 20 % ... 90 %   |
| Permissible humidity (storage/transport) | 30 % ... 70 %   |

## Standards and regulations

# PP-H 1,5/S/1-R - Plug



3212714

<https://www.phoenixcontact.com/us/products/3212714>

|                                  |           |
|----------------------------------|-----------|
| Connection in acc. with standard | IEC 61984 |
|----------------------------------|-----------|

## Mounting

|               |   |
|---------------|---|
| Assembly note | Use of a parallel pressing tool is recommended for easy latching of the COMBI connector and coupling elements for self-assembly |
|---------------|---|

# PP-H 1,5/S/1-R - Plug

3212714

<https://www.phoenixcontact.com/us/products/3212714>




## Drawings

Schematic diagram



Diagram



Circuit diagram



# PP-H 1,5/S/1-R - Plug




3212714


<https://www.phoenixcontact.com/us/products/3212714>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3212714>

|  <b>CSA</b><br>Approval ID: 158887 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B   | 300 V                 | 15 A                  | 26 - 14           | -                           |
| C   | 300 V                 | 15 A                  | 26 - 14           | -                           |
| D   | 600 V                 | 5 A                   | 26 - 14           | -                           |

|  <b>IECEE CB Scheme</b><br>Approval ID: DE1-65179 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine  | 500 V                 | -                     | -                 | 0.14 - 1.5                  |

|  <b>cULus Recognized</b><br>Approval ID: E60425 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| B  | 300 V                 | 15 A                  | 26 - 14           | -                           |
| C  | 300 V                 | 15 A                  | 26 - 14           | -                           |
| D  | 600 V                 | 5 A                   | 26 - 14           | -                           |

|  <b>LR</b><br>Approval ID: LR2371832TA |  |
|---|--|
|---|--|

| <b>ClassNK</b> <b>NK</b><br>Approval ID: 14ME0912 |  |
|---|--|
|---|--|

|  <b>BV</b><br>Approval ID: 39979/B0 BV |  |
|---|--|
|---|--|

|  <b>VDE Gutachten mit Fertigungsüberwachung</b> |  |
|--|--|
|--|--|

# PP-H 1,5/S/1-R - Plug



3212714

<https://www.phoenixcontact.com/us/products/3212714>

Approval ID: 40034766

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 500 V                 | -                     | -                 | -                           |

**DNV**

Approval ID: TAE000010T



**EAC**

Approval ID: KZ7500651131219505

# PP-H 1,5/S/1-R - Plug



3212714

<https://www.phoenixcontact.com/us/products/3212714>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250306 |
| ECLASS-15.0 | 27250306 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002021 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# PP-H 1,5/S/1-R - Plug



3212714

<https://www.phoenixcontact.com/us/products/3212714>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)