STG-MTN 1,5-2,5 BAND - Crimp contact

3190632

https://www.phoenixcontact.com/us/products/3190632

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Module socket contact, inserted in the PCC or HCC plug housing after crimping the conductor, for 1.5 mm^2 ... 2.5 mm^2 conductors, ribbon contact

Commercial data

Item number	3190632
Packing unit	3,300 pc
Minimum order quantity	3,300 pc
Sales key	AA03
Product key	AACCEG
GTIN	4017918100568
Weight per piece (including packing)	0.95 g
Weight per piece (excluding packing)	0.95 g
Customs tariff number	85366990
Country of origin	CN

Technical data

Product properties

Product type	Connector
Product family	Metal
Pitch	0 mm

Electrical properties

Nominal current I_N	10 A

Dimensions

Pitch	-

Material specifications

Contact surface	Tin Sn
Contact surface material	Tin
Metal surface contact area (top layer)	Tin Sn)

Standards and regulations

Connection in acc. with standard	EN-VDE

Classifications

ECLASS

ECLASS-13.0	27469090
ECLASS-15.0	27469090

ETIM

ETIM 10.0	EC002943

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com