

CARRIER 35-13 KIT - Short circuit kit for current transformers




3215067

<https://www.phoenixcontact.com/us/products/3215067>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Short-circuit kit for current transformer. Use with DIN rail mounted RBO/RSC 5 feed-through terminals



Commercial data

Item number	3215067
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1ZWX
GTIN	4046356640930
Weight per piece (including packing)	30 g
Weight per piece (excluding packing)	30 g
Customs tariff number	85369010
Country of origin	CN

CARRIER 35-13 KIT - Short circuit kit for current transformers



3215067

<https://www.phoenixcontact.com/us/products/3215067>

Technical data

Product properties

Product type	Short-circuit connector
Number of positions	12
Pitch	13 mm

Dimensions

Width	13 mm
Height	53.3 mm
Depth on NS 35/7,5	47 mm
Depth on NS 35/15	54.6 mm
Pitch	13 mm

Material specifications

Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

CARRIER 35-13 KIT - Short circuit kit for current transformers



3215067

<https://www.phoenixcontact.com/us/products/3215067>

Classifications

ECLASS

ECLASS-15.0	27250190
ECLASS-13.0	27141190

ETIM

ETIM 10.0	EC002848
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CARRIER 35-13 KIT - Short circuit kit for current transformers



3215067

<https://www.phoenixcontact.com/us/products/3215067>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.732 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com