

CD 100X80 BU - Cable duct



3240324

<https://www.phoenixcontact.com/us/products/3240324>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable duct for installation and mounting in control cabinets, blue, comprising upper part and mounting base, width: 100 mm, height: 80 mm, length: 2000 mm

Your advantages

- Predetermined breaking point enables tool-free, burr-free removal of bars
- Thanks to its leverage and special cutting geometry, the PPS CD cable duct cutter enables easy, burr-free cutting with minimum effort
- Easy, burr-free cutting with minimum effort using the CUTFOX-CD cable duct cutter
- The wide, diagonal heads of the cable duct bars make it easy to fit the cover and hold it securely in place
- Installed conductors are securely held in place by means of wire retaining clips that can be snapped onto bars on the side
- Plastic body-bound rivets enable easy fixing of cable ducts using the rivet setting tool

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3240324 |
| Packing unit | 8 pc |
| Minimum order quantity | 8 pc |
| Sales key | BE74 |
| Product key | BE7432 |
| GTIN | 4046356508049 |
| Weight per piece (including packing) | 1,993 g |
| Weight per piece (excluding packing) | 1,777 g |
| Customs tariff number | 39259020 |
| Country of origin | DE |

CD 100X80 BU - Cable duct



3240324

<https://www.phoenixcontact.com/us/products/3240324>

Technical data

Product properties

| | |
|--------------|-------------|
| Product type | Wiring duct |
|--------------|-------------|

Dimensions

| | |
|--------------------|------------------|
| Width | 100 mm |
| Height | 80 mm |
| Length | 2000 mm |
| Drill hole spacing | 25 mm |
| Hole diameter | 4.5 mm ... 14 mm |

Material specifications

| | |
|--|-----------------|
| Color | blue (RAL 5015) |
| Material | PVC |
| Flammability rating according to UL 94 | V0 |
| Components | Lead-free |

Cable/line

| | |
|--------------|----|
| Halogen-free | no |
|--------------|----|

Mechanical properties

| | |
|--|------------------------------------|
| Usage cross-section | 7174 mm ² (100 %) |
| Number of cables at 60% filling volume | 275 (2.5 mm ² Ø 3.4 mm) |

Technical data

| | |
|--------------------|-------|
| Drill hole spacing | 25 mm |
|--------------------|-------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -25 °C ... 60 °C |
|---------------------------------|------------------|

CD 100X80 BU - Cable duct



3240324

<https://www.phoenixcontact.com/us/products/3240324>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240324>



CSA

Approval ID: 80202282



VDE approval of drawings

Approval ID: 40058456



UL Recognized

Approval ID: E328576

CD 100X80 BU - Cable duct



3240324

<https://www.phoenixcontact.com/us/products/3240324>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27400703 |
| ECLASS-15.0 | 27400703 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000012 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131700 |
|-------------|----------|

CD 100X80 BU - Cable duct



3240324

<https://www.phoenixcontact.com/us/products/3240324>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 3.941 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com