

STIO-IN 2,5/4-PE OG - Installation protective conductor terminal block



3209109

<https://www.phoenixcontact.com/us/products/3209109>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Installation protective conductor terminal block, nom. voltage: 250 V, nominal current: 30 A, number of connections: 5, connection method: Spring-cage connection, Rated cross section: 2.5 mm², cross section: 0.08 mm² - 4 mm², mounting type: NS 35/7,5, NS 35/15, color: orange

Your advantages

- Upper level for signal wiring

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3209109 |
| Packing unit | 25 pc |
| Minimum order quantity | 25 pc |
| Sales key | BE02 |
| Product key | BE2118 |
| GTIN | 4046356143295 |
| Weight per piece (including packing) | 19.264 g |
| Weight per piece (excluding packing) | 16.834 g |
| Customs tariff number | 85369010 |
| Country of origin | TR |

STIO-IN 2,5/4-PE OG - Installation protective conductor terminal block



3209109

<https://www.phoenixcontact.com/us/products/3209109>

Technical data

Product properties

| | |
|-----------------------|--------------------------------|
| Product type | Sensor/actuator terminal block |
| Number of connections | 5 |
| Number of rows | 3 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|---|--------|
| Rated surge voltage | 4 kV |
| Maximum power dissipation for nominal condition | 0.77 W |

Connection data

| | |
|---|---|
| Grounding foot | Yes |
| Number of connections per level | 5 |
| Nominal cross section | 2.5 mm ² |
| Connection method | Spring-cage connection |
| Note | Please observe the current carrying capacity of the DIN rails. |
| Stripping length | 8 mm ... 10 mm |
| Internal cylindrical gage | A3 |
| Connection in acc. with standard | IEC 60947-7-1/IEC 60947-7-2 |
| Conductor cross-section rigid | 0.08 mm ² ... 4 mm ² |
| Cross section AWG | 28 ... 12 (converted acc. to IEC) |
| Conductor cross-section flexible | 0.08 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible [AWG] | 28 ... 14 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.14 mm ² ... 2.5 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.14 mm ² ... 2.5 mm ² |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm ² |
| Nominal cross section | 2.5 mm ² |
| Nominal current | 30 A (For central infeed and 4 mm ² conductor cross-section) 18 A (For single-sided infeed and 2.5 mm ² conductor cross-section) |
| Maximum load current | 30 A (with 4 mm ² conductor cross-section) |
| Nominal voltage | 250 V |

Dimensions

| | |
|-----------------|---------|
| Width | 10.4 mm |
| End cover width | 2.2 mm |
| Height | 92.3 mm |

STIO-IN 2,5/4-PE OG - Installation protective conductor terminal block



3209109

<https://www.phoenixcontact.com/us/products/3209109>

| | |
|--------------------|---------|
| Depth on NS 35/7,5 | 44.5 mm |
| Depth on NS 35/15 | 52 mm |

Material specifications

| | |
|---|-------------------|
| Color | orange (RAL 2003) |
| Flammability rating according to UL 94 | V0 |
| Insulating material group | I |
| Insulating material | PA |
| Static insulating material application in cold | -60 °C |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Calorimetric heat release NFPA 130 (ASTM E 1354) | 28 MJ/kg |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Electrical tests

Surge voltage test

| | |
|-----------------------|-------------|
| Test voltage setpoint | 4.8 kV |
| Result | Test passed |

Temperature-rise test

| | |
|--|-------------------------------------|
| Requirement temperature-rise test | Increase in temperature \leq 45 K |
| Result | Test passed |
| Short-time withstand current 2.5 mm ² | 0.3 kA |
| Result | Test passed |

Power-frequency withstand voltage

| | |
|-----------------------|-------------|
| Test voltage setpoint | 1.5 kV |
| Result | Test passed |

Mechanical properties

Mechanical data

| | |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

Mechanical tests

Mechanical strength

| | |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

STIO-IN 2,5/4-PE OG - Installation protective conductor terminal block



3209109

<https://www.phoenixcontact.com/us/products/3209109>

Attachment on the carrier

| | |
|-------------------------|-------------|
| DIN rail/fixing support | NS 35 |
| Test force setpoint | 1 N |
| Result | Test passed |

Test for conductor damage and slackening

| | |
|--------------------------------|-------------------------------|
| Rotation speed | 10 rpm |
| Revolutions | 135 |
| Conductor cross-section/weight | 0.08 mm ² / 0.1 kg |
| | 2.5 mm ² / 0.7 kg |
| | 4 mm ² / 0.9 kg |
| Result | Test passed |

Environmental and real-life conditions

Aging

| | |
|--------------------|-------------|
| Temperature cycles | 192 |
| Result | Test passed |

Needle-flame test

| | |
|------------------|-------------|
| Time of exposure | 30 s |
| Result | Test passed |

Ambient conditions

| | |
|--|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Standards and regulations

| | |
|----------------------------------|-----------------------------|
| Connection in acc. with standard | IEC 60947-7-1/IEC 60947-7-2 |
|----------------------------------|-----------------------------|

Mounting

| | |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
| | NS 35/15 |


STIO-IN 2,5/4-PE OG - Installation protective conductor terminal block

3209109

<https://www.phoenixcontact.com/us/products/3209109>

Drawings

Circuit diagram



STIO-IN 2,5/4-PE OG - Installation protective conductor terminal block



3209109

<https://www.phoenixcontact.com/us/products/3209109>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3209109>



EAC

Approval ID: RU C-DE.BL08.B.00644



cULus Recognized

Approval ID: E60425

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| B | 300 V | 10 A | 28 - 12 | - |
| C | 150 V | 20 A | 28 - 12 | - |
| D | 300 V | 10 A | 28 - 12 | - |



EAC

Approval ID: KZ7500651131219505

STIO-IN 2,5/4-PE OG - Installation protective conductor terminal block



3209109

<https://www.phoenixcontact.com/us/products/3209109>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250112 |
| ECLASS-15.0 | 27250112 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000900 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

STIO-IN 2,5/4-PE OG - Installation protective conductor terminal block



3209109

<https://www.phoenixcontact.com/us/products/3209109>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.102 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com