

STIO-IN 2,5/3 OG - Power terminal block



3209196

<https://www.phoenixcontact.com/us/products/3209196>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power terminal block, nom. voltage: 250 V, nominal current: 30 A, number of connections: 2, connection method: Spring-cage connection, Rated cross section: 2.5 mm², cross section: 0.08 mm² - 4 mm², mounting type: NS 35/7,5, NS 35/15, color: orange

Your advantages

- Three-conductor output terminal block of the same shape with PE connection in the lower level for wiring actuators
- Power terminal blocks can be located at any point on the terminal strip for supply or extension purposes
- Versions with LED for indicating the switching states
- Easy bridging and potential distribution using the patented plug-in bridges from the CLIPLINE complete system
- Potential is supplied via the STIO-IN power terminal blocks
- For space and time-saving wiring of three-conductor initiators and actuators
- The upper level is for signal wiring, whereas the two lower levels are used to distribute the positive and negative potential

Commercial data

Item number	3209196
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BE02
Product key	BE2117
GTIN	4046356181709
Weight per piece (including packing)	13.42 g
Weight per piece (excluding packing)	13.42 g
Customs tariff number	85369010
Country of origin	TR

STIO-IN 2,5/3 OG - Power terminal block



3209196

<https://www.phoenixcontact.com/us/products/3209196>

Technical data

Product properties

Product type	Sensor/actuator terminal block
Number of connections	2
Number of rows	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	4 kV
Maximum power dissipation for nominal condition	0.77 W

Connection data

Number of connections per level	1
Nominal cross section	2.5 mm ²
Connection method	Spring-cage connection
Stripping length	8 mm ... 10 mm
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	0.08 mm ² ... 4 mm ²
Cross section AWG	28 ... 12 (converted acc. to IEC)
Conductor cross-section flexible	0.08 mm ² ... 2.5 mm ²
Conductor cross-section, flexible [AWG]	28 ... 14 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.14 mm ² ... 2.5 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.14 mm ² ... 2.5 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm ²
Nominal cross section	2.5 mm ²
Nominal current	30 A (For central infeed and 4 mm ² conductor cross-section) 18 A (For single-sided infeed and 2.5 mm ² conductor cross-section)
Maximum load current	30 A (with 4 mm ² conductor cross-section)
Nominal voltage	250 V

Dimensions

Width	10.4 mm
End cover width	2.2 mm
Height	75 mm
Depth on NS 35/7,5	44.5 mm
Depth on NS 35/15	52 mm

Material specifications

Color	orange (RAL 2003)
-------	-------------------

STIO-IN 2,5/3 OG - Power terminal block



3209196

<https://www.phoenixcontact.com/us/products/3209196>

Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

Mounting

Mounting type	NS 35/7,5
	NS 35/15

STIO-IN 2,5/3 OG - Power terminal block

3209196

<https://www.phoenixcontact.com/us/products/3209196>



Drawings

Circuit diagram



STIO-IN 2,5/3 OG - Power terminal block



3209196

<https://www.phoenixcontact.com/us/products/3209196>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3209196>



EAC

Approval ID: RU C-DE.BL08.B.00644



cULus Recognized

Approval ID: E60425

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	300 V	10 A	28 - 12	-
C				
	150 V	20 A	28 - 12	-
D				
	300 V	10 A	28 - 12	-



EAC

Approval ID: KZ7500651131219505

STIO-IN 2,5/3 OG - Power terminal block



3209196

<https://www.phoenixcontact.com/us/products/3209196>

Classifications

ECLASS

ECLASS-13.0	27250112
ECLASS-15.0	27250112

ETIM

ETIM 10.0	EC000900
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

STIO-IN 2,5/3 OG - Power terminal block



3209196

<https://www.phoenixcontact.com/us/products/3209196>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.095 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com