

# P-FU 5X20 LED 24-5 120KOHM - Fuse plug



3209240

<https://www.phoenixcontact.com/us/products/3209240>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Fuse plug, nom. voltage: 24 V, nominal current: 6.3 A, fuse type: G / 5 x 20, color: black



## Your advantages

- Large-surface labeling option

## Commercial data

Item number	3209240
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z3X
GTIN	4046356773478
Weight per piece (including packing)	5.33 g
Weight per piece (excluding packing)	4.836 g
Customs tariff number	85369095
Country of origin	CN

# P-FU 5X20 LED 24-5 120KOHM - Fuse plug



3209240

<https://www.phoenixcontact.com/us/products/3209240>

## Technical data

### Notes

General	Suitable for terminal blocks with a width of 5.2 mm and above with TG zone
Notes on operation	Prior to replacing the cartridge fuse, disconnect the fuse connector from the basic terminal block.

### Product properties

Product type	Fuse
Potentials	1

### Insulation characteristics

Degree of pollution	3
---------------------	---

### Electrical properties

Fuse	G / 5 x 20
LED voltage range	12 V DC ... 30 V DC
LED current range	0.35 mA ... 0.95 mA

### Input data

LED voltage range	12 V DC ... 30 V DC
-------------------	---------------------

### Connection data

Nominal current	6.3 A (the current is determined by the fuse used)
Maximum load current	6.3 A (the current is determined by the fuse used)
Nominal voltage	24 V (The current is determined by the fuse used, the voltage by the fuse or selected LED display.)

### Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V0
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

### Environmental and real-life conditions

#### Ambient conditions

# P-FU 5X20 LED 24-5 120KOHM - Fuse plug



3209240

<https://www.phoenixcontact.com/us/products/3209240>

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

# P-FU 5X20 LED 24-5 120KOHM - Fuse plug


3209240

<https://www.phoenixcontact.com/us/products/3209240>



## Drawings

Circuit diagram



# P-FU 5X20 LED 24-5 120KOHM - Fuse plug





3209240


<https://www.phoenixcontact.com/us/products/3209240>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3209240>

 <b>CSA</b> Approval ID: 158887				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
	300 V	10 A	-	-

 <b>EAC</b> Approval ID: RU C-DE.BL08.B.00714				
---	--	--	--	--

 <b>cULus Recognized</b> Approval ID: E60425				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $mm^2$
keine				
	300 V	10 A	-	-

# P-FU 5X20 LED 24-5 120KOHM - Fuse plug



3209240

<https://www.phoenixcontact.com/us/products/3209240>

## Classifications

### ECLASS

ECLASS-13.0	27250305
ECLASS-15.0	27250305

### ETIM

ETIM 10.0	EC002018
-----------	----------

### UNSPSC

UNSPSC 21.0	39121600
-------------	----------

# P-FU 5X20 LED 24-5 120KOHM - Fuse plug



3209240

<https://www.phoenixcontact.com/us/products/3209240>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.098 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)