# WT-STEEL S 7,9X259 - Cable tie

3240814

https://www.phoenixcontact.com/us/products/3240814

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable binders, made from rust-free stainless steel (AISI 304), suitable for harsh ambient conditions, with ball lock, for quick and secure bundling and fastening

## Commercial data

| | |
|---|---|
| Item number | 3240814 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | BE07 |
| Product key | BE7132 |
| GTIN | 4046356705622 |
| Weight per piece (including packing) | 5.87 g |
| Weight per piece (excluding packing) | 5.87 g |
| Customs tariff number | 73269098 |
| Country of origin | GB |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Cable tie |
| Tensile strength GRP | 1335 N |

### Dimensions

| | |
|---|---|
| Width | 7.9 mm |
| Length | 259 mm |
| Max. material thickness | 0.25 mm |

### Material specifications

| | |
|---|---|
| RoHS compliant | yes |
| Color | silver-colored |
| Material | Stainless steel 1.4301/AISI 304 |
| Components | free from silicone and halogen |

### Cable/line

| | |
|---|---|
| External cable diameter | ≤ 69.00 mm |
| Tensile strength | 1335 N |

### Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -80 °C ... 538 °C |
| Ambient temperature (assembly) | -80 °C ... 538 °C |
| Resistance to UV radiation | yes |
| Recommended storage conditions | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |

### Mounting

| | |
|---|---|
| Mounting type | Cannot be removed |

## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/3240814

**cULus Listed**
Approval ID: E328576

**DNV**
Approval ID: TAE000057Y

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27140702 |
| ECLASS-15.0 | 27140702 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000046 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121700 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com