WP-SC PA HF 28,5 BK - Cable protection end sleeve

3240985

https://www.phoenixcontact.com/us/products/3240985

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable protection end sleeve, material: PA 6, color: black, flammability rating in acc. with UL 94: V2, inside diameter: 20.8 mm

Commercial data

Item number	3240985
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BF68
Product key	AF7DSA
GTIN	4046356711036
Weight per piece (including packing)	4.256 g
Weight per piece (excluding packing)	3.294 g
Customs tariff number	39174000
Country of origin	DE

Technical data

Product properties

Product type	Protective cap

Dimensions

Length	22 mm
Diameter	28.5 mm

Internal dimensions

Internal diameter	20.8 mm

Material specifications

Material	PA 6
Flammability rating according to UL 94	V2
Components	halogen-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/3240985

UL Recognized
Approval ID: E86359

LR

Classifications

ECLASS

ECLASS-15.0	27430316
ECLASS-13.0	27430316

ETIM

ETIM 10.0	EC000519

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.386 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com