


# UTN 10 - N disconnect terminal block



3245040

<https://www.phoenixcontact.com/us/products/3245040>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



## N disconnect terminal block, **Assembly instruction:**

In order to securely fix the neutral busbar in place, support brackets must be placed at the beginning and end of each terminal strip as well as every 20 cm on longer terminal strips.

The corresponding support brackets can be found at [phoenixcontact.com/products](https://www.phoenixcontact.com/products), for neutral conductor disconnection, nom. voltage: 400 V, nominal current: 57 A, Screw connection, Rated cross section: 10 mm<sup>2</sup>, cross section: 0.5 mm<sup>2</sup> - 16 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, color: blue

## Your advantages

- Same shape as UT standard terminal blocks

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3245040       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE01          |
| Product key                          | BE1152        |
| GTIN                                 | 4046356299015 |
| Weight per piece (including packing) | 19.914 g      |
| Weight per piece (excluding packing) | 19.6 g        |
| Customs tariff number                | 85369010      |
| Country of origin                    | PL            |

# UTN 10 - N disconnect terminal block



3245040

<https://www.phoenixcontact.com/us/products/3245040>

## Technical data

### Notes

|         |  |
|---------|--|
| General | <b>Assembly instruction:</b><br>In order to securely fix the neutral busbar in place, support brackets must be placed at the beginning and end of each terminal strip as well as every 20 cm on longer terminal strips. The corresponding support brackets can be found at <a href="https://www.phoenixcontact.com/products">phoenixcontact.com/products</a> |
|---------|--|

### Product properties

|                       |                             |
|-----------------------|-----------------------------|
| Product type          | Installation terminal block |
| Number of connections | 1                           |
| Number of rows        | 1                           |
| Potentials            | 1                           |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|   |        |
|---|--------|
| Rated surge voltage                             | 6 kV   |
| Maximum power dissipation for nominal condition | 1.82 W |
| Current carrying capacity of the neutral busbar | 140 A  |

### Connection data

|                                 |                    |
|---------------------------------|--------------------|
| Number of connections per level | 2                  |
| Nominal cross section           | 10 mm <sup>2</sup> |

### Level 1 above 1 below 1

|   |   |
|---|---|
| Connection method   | Screw connection                            |
| Screw thread  | M4  |
| Tightening torque   | 1.5 ... 1.8 Nm                              |
| Stripping length  | 10 mm                                       |
| Connection in acc. with standard  | IEC 60947-7-1                               |
| Conductor cross-section rigid   | 0.5 mm <sup>2</sup> ... 16 mm <sup>2</sup>  |
| Cross section AWG   | 20 ... 6 (converted acc. to IEC)            |
| Conductor cross-section flexible  | 0.5 mm <sup>2</sup> ... 16 mm <sup>2</sup>  |
| Conductor cross-section, flexible [AWG]   | 20 ... 6 (converted acc. to IEC)            |
| Conductor cross-section flexible (ferrule without plastic sleeve)                   | 0.5 mm <sup>2</sup> ... 10 mm <sup>2</sup>  |
| Flexible conductor cross-section (ferrule with plastic sleeve)                      | 0.5 mm <sup>2</sup> ... 10 mm <sup>2</sup>  |
| 2 conductors with same cross section, rigid   | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| 2 conductors with same cross section, flexible                                      | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve | 0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| 2 conductors with the same cross section, flexible, with TWIN                       | 0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>   |

# UTN 10 - N disconnect terminal block



3245040

<https://www.phoenixcontact.com/us/products/3245040>

|                             |                    |
|-----------------------------|--------------------|
| ferrule with plastic sleeve |                    |
| Nominal cross section       | 10 mm <sup>2</sup> |
| Nominal current             | 57 A               |
| Maximum load current        | 57 A               |
| Nominal voltage             | 400 V              |

## Dimensions

|                    |         |
|--------------------|---------|
| Width              | 10.2 mm |
| End cover width    | 2.2 mm  |
| Height             | 55 mm   |
| Depth              | 46.9 mm |
| Depth on NS 35/7,5 | 47.5 mm |
| Depth on NS 35/15  | 55 mm   |

## Material specifications

|  |                 |
|--|-----------------|
| Color  | blue (RAL 5015) |
| Flammability rating according to UL 94                           | V0              |
| Insulating material group  | I               |
| Insulating material  | PA              |
| Static insulating material application in cold                   | -60 °C          |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22           | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23           | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24           | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26           | HL 1 - HL 3     |
| Surface flammability NFPA 130 (ASTM E 162)                       | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)          | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                           | passed          |

## Electrical tests

### Surge voltage test

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 7.3 kV      |
| Result                | Test passed |

### Temperature-rise test

|   |                                |
|---|--------------------------------|
| Requirement temperature-rise test               | Increase in temperature ≤ 45 K |
| Result  | Test passed                    |
| Short-time withstand current 10 mm <sup>2</sup> | 1.2 kA                         |
| Result  | Test passed                    |

### Power-frequency withstand voltage

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 1.89 kV     |
| Result                | Test passed |

## Mechanical properties

# UTN 10 - N disconnect terminal block



3245040

<https://www.phoenixcontact.com/us/products/3245040>

## Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Mechanical tests

### Mechanical strength

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

### Attachment on the carrier

|                     |             |
|---------------------|-------------|
| Test force setpoint | 5 N         |
| Result              | Test passed |

### Test for conductor damage and slackening

|                                |                              |
|--------------------------------|------------------------------|
| Rotation speed                 | 10 (+/- 2) rpm               |
| Revolutions                    | 135                          |
| Conductor cross-section/weight | 0.5 mm <sup>2</sup> / 0.3 kg |
|                                | 10 mm <sup>2</sup> / 2 kg    |
|                                | 16 mm <sup>2</sup> / 2.9 kg  |
| Result                         | Test passed                  |

## Environmental and real-life conditions

### Aging

|                    |             |
|--------------------|-------------|
| Temperature cycles | 192         |
| Result             | Test passed |

### Needle-flame test

|                  |             |
|------------------|-------------|
| Time of exposure | 30 s        |
| Result           | Test passed |

### Oscillation/broadband noise

|                        |  |
|------------------------|--|
| Specification          | DIN EN 50155 (VDE 0115-200):2018-05            |
| Spectrum               | Long life test category 2, bogie-mounted       |
| Frequency              | $f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$ |
| ASD level              | 6.12 (m/s <sup>2</sup> ) <sup>2</sup> /Hz      |
| Acceleration           | 3.12g  |
| Test duration per axis | 5 h  |
| Test directions        | X-, Y- and Z-axis                              |
| Result                 | Test passed                                    |

### Shocks

|                                |                                   |
|--------------------------------|-----------------------------------|
| Pulse shape                    | Half-sine                         |
| Acceleration                   | 5g                                |
| Shock duration                 | 30 ms                             |
| Number of shocks per direction | 3                                 |
| Test directions                | X-, Y- and Z-axis (pos. and neg.) |
| Result                         | Test passed                       |

# UTN 10 - N disconnect terminal block



3245040

<https://www.phoenixcontact.com/us/products/3245040>

## Ambient conditions

|  |  |
|--|--|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)  |
| Ambient temperature (assembly)           | -5 °C ... 70 °C  |
| Permissible humidity (operation)         | 20 % ... 90 %  |
| Permissible humidity (storage/transport) | 30 % ... 70 %  |

## Standards and regulations

|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |

# UTN 10 - N disconnect terminal block

3245040

<https://www.phoenixcontact.com/us/products/3245040>



## Drawings

### Circuit diagram



# UTN 10 - N disconnect terminal block



3245040

<https://www.phoenixcontact.com/us/products/3245040>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3245040>



**EAC**

Approval ID: KZ7500651131219505

# UTN 10 - N disconnect terminal block



3245040

<https://www.phoenixcontact.com/us/products/3245040>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250111 |
| ECLASS-15.0 | 27250111 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001257 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# UTN 10 - N disconnect terminal block



3245040

<https://www.phoenixcontact.com/us/products/3245040>

## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 6(c) |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 18032a42-8e44-4b17-8b3a-c645b38a2b70 |

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.082 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)