

# PP-H 4/ 3 - Plug

3212022

<https://www.phoenixcontact.com/us/products/3212022>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug, nom. voltage: 800 V, nominal current: 32 A, number of connections: 3, number of positions: 3, connection method: Push-in connection, Rated cross section: 4 mm<sup>2</sup>, 1st level connection left, cross section: 0.2 mm<sup>2</sup> - 6 mm<sup>2</sup>, color: gray

## Your advantages

- Large-surface labeling option
- The Push-in technology COMBI plugs for self-assembly provide solutions that users can implement themselves
- Tested for railway applications

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3212022       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE22          |
| Product key                          | BE2244        |
| GTIN                                 | 4046356483070 |
| Weight per piece (including packing) | 14.81 g       |
| Weight per piece (excluding packing) | 14.72 g       |
| Customs tariff number                | 85366990      |
| Country of origin                    | PL            |

## Technical data

### Notes

|                    |   |
|--------------------|---|
| Notes on operation | COMBI connectors are connectors without switching power in accordance with IEC 61984 and can be connected or disconnected without load or voltage when used as intended |
|--------------------|---|

### Product properties

|                       |                   |
|-----------------------|-------------------|
| Product type          | Terminal plug     |
| Area of application   | Railway industry  |
|                       | Machine building  |
|                       | Plant engineering |
| Number of positions   | 3                 |
| Pitch                 | 6.2 mm            |
| Number of connections | 3                 |
| Number of rows        | 1                 |
| Potentials            | 3                 |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|   |        |
|---|--------|
| Rated surge voltage                             | 8 kV   |
| Maximum power dissipation for nominal condition | 1.02 W |

### Connection data

|                                 |                   |
|---------------------------------|-------------------|
| Number of connections per level | 3                 |
| Nominal cross section           | 4 mm <sup>2</sup> |

#### 1st level connection left

|   |  |
|---|--|
| Connection method   | Push-in connection                         |
| Stripping length  | 10 mm ... 12 mm                            |
| Internal cylindrical gage   | A4   |
| Connection in acc. with standard  | IEC 61984                                  |
| Conductor cross-section rigid   | 0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup>  |
| Cross section AWG   | 24 ... 10 (converted acc. to IEC)          |
| Conductor cross-section flexible  | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>  |
| Conductor cross-section, flexible [AWG]   | 24 ... 12 (converted acc. to IEC)          |
| Conductor cross-section flexible (ferrule without plastic sleeve)                         | 0.25 mm <sup>2</sup> ... 4 mm <sup>2</sup> |
| Flexible conductor cross-section (ferrule with plastic sleeve)                            | 0.25 mm <sup>2</sup> ... 4 mm <sup>2</sup> |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm <sup>2</sup> ... 1 mm <sup>2</sup>  |
| Nominal cross section   | 4 mm <sup>2</sup>                          |
| Nominal current   | 32 A                                       |

# PP-H 4/ 3 - Plug



3212022

<https://www.phoenixcontact.com/us/products/3212022>

|                      |   |
|----------------------|---|
| Maximum load current | 32 A (with 6 mm <sup>2</sup> conductor cross-section) |
| Nominal voltage      | 800 V   |

1st level connection left Connection cross sections directly pluggable

|   |   |
|---|---|
| Conductor cross-section rigid                                     | 0.5 mm <sup>2</sup> ... 6 mm <sup>2</sup> |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup> |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup> |

## Dimensions

|        |         |
|--------|---------|
| Width  | 18.6 mm |
| Height | 21 mm   |
| Depth  | 42.3 mm |
| Pitch  | 6.2 mm  |

## Material specifications

|   |                 |
|---|-----------------|
| Color   | gray (RAL 7042) |
| Flammability rating according to UL 94                                  | V0              |
| Insulating material group   | I               |
| Insulating material   | PA              |
| Static insulating material application in cold                          | -60 °C          |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C          |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C          |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3     |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3     |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 28 MJ/kg        |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed          |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed          |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed          |

## Mechanical properties

Mechanical data

|                 |    |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

## Environmental and real-life conditions

Ambient conditions

|   |   |
|---|---|
| Ambient temperature (operation)         | -60 °C (max. operating temperature see derating curve)                    |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)          | -5 °C ... 70 °C   |
| Ambient temperature (actuation)         | -5 °C ... 70 °C   |
| Permissible humidity (operation)        | 20 % ... 90 %   |

# PP-H 4/ 3 - Plug



3212022

<https://www.phoenixcontact.com/us/products/3212022>

|  |               |
|--|---------------|
| Permissible humidity (storage/transport) | 30 % ... 70 % |
|--|---------------|

## Standards and regulations

|                                  |           |
|----------------------------------|-----------|
| Connection in acc. with standard | IEC 61984 |
|----------------------------------|-----------|

# PP-H 4/ 3 - Plug


3212022

<https://www.phoenixcontact.com/us/products/3212022>



## Drawings

Schematic diagram



Diagram



Circuit diagram



# PP-H 4/ 3 - Plug



3212022

<https://www.phoenixcontact.com/us/products/3212022>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3212022>

### DNV

Approval ID: TAE000010T



### IECEE CB Scheme

Approval ID: DE1-64672\_B1\_B2

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 800 V                 | 32 A                  | -                 | -                           |



### cULus Recognized

Approval ID: E60425

|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| C |                       |                       |                   |                             |
|   | 600 V                 | 28 A                  | 24 - 10           | -                           |



### BV

Approval ID: 39979/B0 BV



### VDE Zeichengenehmigung

Approval ID: 40043445

|                          | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|--------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine                    |                       |                       |                   |                             |
| Only flexible conductors | 800 V                 | 32 A                  | -                 | 0.2 - 4                     |



### EAC

Approval ID: KZ7500651131219505

# PP-H 4/ 3 - Plug



3212022

<https://www.phoenixcontact.com/us/products/3212022>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250306 |
| ECLASS-15.0 | 27250306 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002021 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# PP-H 4/ 3 - Plug



3212022

<https://www.phoenixcontact.com/us/products/3212022>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)