

PTPOWER 35-3L/N/FE-F - High-current terminal block



3212076

<https://www.phoenixcontact.com/us/products/3212076>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



High-current terminal block, Blocked, nom. voltage: 1000 V, nominal current: 125 A, number of connections: 10, number of positions: 5, connection method: PowerTurn connection, Rated cross section: 35 mm², cross section: 2.5 mm² - 35 mm², mounting type: direct screw connection, color: gray/blue/black-yellow

Your advantages

- Quick and easy connection is now also possible for large conductors with the high-current terminal block
- In addition to the testing option in the double function shaft, all terminal blocks provide an additional test pick-off
- The compact design and front connection enable wiring in a confined space
- The Push-in connection terminal blocks are characterized by the system features of the CLIPLINE complete system and by easy and tool-free wiring of conductors with ferrules or solid conductors

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3212076 |
| Packing unit | 2 pc |
| Minimum order quantity | 2 pc |
| Sales key | BE22 |
| Product key | BE2211 |
| GTIN | 4046356869812 |
| Weight per piece (including packing) | 461 g |
| Weight per piece (excluding packing) | 444 g |
| Customs tariff number | 85369010 |
| Country of origin | TR |

3212076

<https://www.phoenixcontact.com/us/products/3212076>

Technical data

Product properties

| | |
|-----------------------|-----------------------------|
| Product type | High current terminal block |
| Number of positions | 5 |
| Pitch | 16 mm |
| Number of connections | 10 |
| Number of rows | 1 |
| Potentials | 5 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|---|--------|
| Rated surge voltage | 8 kV |
| Maximum power dissipation for nominal condition | 4.06 W |

Connection data

| | |
|---|---|
| Number of connections per level | 10 |
| Nominal cross section | 35 mm ² |
| Rated cross section AWG | 2 |
| Connection method | PowerTurn connection |
| Stripping length | 25 mm |
| Conductor cross-section rigid | 2.5 mm ² ... 35 mm ² |
| Cross section AWG | 12 ... 2 (converted acc. to IEC) |
| Conductor cross-section flexible | 2.5 mm ² ... 35 mm ² |
| Conductor cross-section, flexible [AWG] | 12 ... 2 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 2.5 mm ² ... 35 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 2.5 mm ² ... 35 mm ² |
| Nominal cross section | 35 mm ² |
| Nominal current | 125 A |
| Maximum load current | 125 A (with 35 mm ² conductor cross-section) |
| Nominal voltage | 1000 V |

Connection cross sections directly pluggable

| | |
|---|--|
| Conductor cross-section rigid | 2.5 mm ² ... 35 mm ² |
| Conductor cross-section, rigid [AWG] | 12 ... 2 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 2.5 mm ² ... 35 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 2.5 mm ² ... 35 mm ² |

Ex data

Rated data (ATEX/IECEx)

| | |
|----------------|------------------------|
| Identification | Ⓔ II 2 GD Ex eb IIC Gb |
|----------------|------------------------|

PTPOWER 35-3L/N/FE-F - High-current terminal block



3212076

<https://www.phoenixcontact.com/us/products/3212076>

| | |
|-----------------------------|-------------------------------------|
| Operating temperature range | -60 °C ... 110 °C |
| Ex-certified accessories | 1206612 SZF 3-1,0X5,5 |
| | 1201662 E/AL-NS 35 |
| List of bridges | Plug-in bridge / FBS 2-16 / 3005963 |
| Bridge data | 89 A (25 mm ²) |
| Ex temperature increase | 40 K (120 A/35 mm ²) |
| for bridging with bridge | 690 V |
| Rated insulation voltage | 660 V |
| output | (Permanent) |


Ex level General

| | |
|----------------------|---------|
| Rated voltage | 690 V |
| Rated current | 109 A |
| Maximum load current | 109 A |
| Contact resistance | 0.16 mΩ |

Ex connection data General

| | |
|--|--|
| Ferrule length | 25 mm |
| Stripping length | 25 mm |
| Nominal cross section | 35 mm ² |
| Rated cross section AWG | 2 |
| Connection capacity rigid | 2.5 mm ² ... 35 mm ² |
| Connection capacity AWG | 12 ... 2 |
| Conductor cross-section flexible, with ferrule without plastic sleeve min. | 6 mm ² |
| Conductor cross-section flexible, with ferrule without plastic sleeve max. | 35 mm ² |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 80 mm |
| Height | 120.2 mm |
| Depth | 68.3 mm |
| Drill hole spacing | 108 mm |
| Hole diameter | 5.5 mm |
| Pitch | 16 mm |

Material specifications

| | |
|-------|----------------------|
| Color | multicolored (RAL -) |
| | gray (RAL 7042) |
| | blue (RAL 5015) |

PTPOWER 35-3L/N/FE-F - High-current terminal block



3212076

<https://www.phoenixcontact.com/us/products/3212076>

| | |
|---|-------------------|
| | black (RAL 9005) |
| | yellow (RAL 1018) |
| Flammability rating according to UL 94 | V0 |
| Insulating material group | I |
| Insulating material | PA |
| Static insulating material application in cold | -60 °C |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 125 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Calorimetric heat release NFPA 130 (ASTM E 1354) | 27,5 MJ/kg |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Mechanical properties

Mechanical data

| | |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

Technical data

| | |
|--------------------|--------|
| Drill hole spacing | 108 mm |
|--------------------|--------|

Environmental and real-life conditions

Ambient conditions

| | |
|--|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Mounting

| | |
|---------------|-------------------------|
| Mounting type | direct screw connection |
|---------------|-------------------------|


PTPOWER 35-3L/N/FE-F - High-current terminal block



3212076

<https://www.phoenixcontact.com/us/products/3212076>

Drawings



PTPOWER 35-3L/N/FE-F - High-current terminal block

3212076


<https://www.phoenixcontact.com/us/products/3212076>

Schematic diagram


PTPOWER



| | | |
|----------------|--|-------|
| AGK 10-PTPOWER | 0,5 mm ² ... 16 mm ² | 18 mm |
| PTPOWER 35 | 2,5 mm ² ... 35 mm ² | 25 mm |
| PTPOWER 50 | 10 mm ² ... 50 mm ² | 32 mm |
| PTPOWER 95 | 25 mm ² ... 95 mm ² | 40 mm |
| PTPOWER 185 | 95 mm ² ... 185 mm ² | 40 mm |



Circuit diagram



PTPOWER 35-3L/N/FE-F - High-current terminal block




3212076

<https://www.phoenixcontact.com/us/products/3212076>


Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3212076>


|  CSA Approval ID: 13631 | | | | |
|--|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| B | 600 V | 115 A | 14 - 2 | - |
| C | 1000 V | 115 A | 14 - 2 | - |


|  EAC Approval ID: RU C-DE.BL08.B.00644 | | | | |
|---|--|--|--|--|
|---|--|--|--|--|


| DNV Approval ID: TAE0000029 | | | | |
|---------------------------------------|--|--|--|--|
|---------------------------------------|--|--|--|--|

|  cUL Recognized Approval ID: E60425 | | | | |
|--|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| C | 1000 V | 115 A | 14 - 2 | - |

|  UL Recognized Approval ID: E60425 | | | | |
|---|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| E | 1000 V | 115 A | 14 - 2 | - |

|  EAC Approval ID: KZ7500651131219505 | | | | |
|---|--|--|--|--|
|---|--|--|--|--|

|  UKCA-EX Approval ID: CML 22UKEX1227U | | | | |
|--|--|--|--|--|
|--|--|--|--|--|

|  IECEx Approval ID: IECExSEV14.0013U | | | | |
|---|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |


PPOWER 35-3L/N/FE-F - High-current terminal block



3212076

<https://www.phoenixcontact.com/us/products/3212076>

| | | | | |
|-----------------------------|-------|-------|---|----------|
| Only rigid conductors | 690 V | 109 A | - | 2.5 - 35 |
| multi-stranded with ferrule | 690 V | 109 A | - | 6 - 35 |

|  ATEX Approval ID: SEV14ATEX0156U | | | | |
|--|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| Only rigid conductors | 690 V | 109 A | - | 2.5 - 35 |
| multi-stranded with ferrule | 690 V | 109 A | - | 6 - 35 |

3212076

<https://www.phoenixcontact.com/us/products/3212076>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250101 |
| ECLASS-15.0 | 27250101 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000897 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

PTPOWER 35-3L/N/FE-F - High-current terminal block



3212076

<https://www.phoenixcontact.com/us/products/3212076>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|--------------|
| CO2e kg | 6.02 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com