# RB ST 10-1,5/S - Reducing bridge

3213252

https://www.phoenixcontact.com/us/products/3213252

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Reducing bridge, pitch: 3.5 mm, number of positions: 2, length: 36 mm, color: red

## Commercial data

| | |
|---|---|
| Item number | 3213252 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE29 |
| Product key | BE2Z2X |
| GTIN | 4046356701686 |
| Weight per piece (including packing) | 4.21 g |
| Weight per piece (excluding packing) | 4.21 g |
| Customs tariff number | 85366990 |
| Country of origin | PL |

## Technical data

### Product properties

| | |
|---|---|
| Product type | Reducing bridge |
| Number of positions | 2 |
| Pitch | 3.5 mm |

### Dimensions

| | |
|---|---|
| Width | 13.9 mm |
| Height | 36.3 mm |
| Depth | 3 mm |
| Length | 36.3 mm |
| Pitch | 3.5 mm |

### Material specifications

| | |
|---|---|
| Color | red (RAL 3001) |
| Flammability rating according to UL 94 | V0 |

### Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C ( ) |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27250303 |
| ECLASS-15.0 | 27250303 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000489 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121400 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com