


EC 16 TR - Europe connectors



3240181

<https://www.phoenixcontact.com/us/products/3240181>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Polyamide Europe terminal strip, transparent, for connecting solid conductors and stranded conductors with ferrules with a cross section of 6 to 16 mm²

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 3240181 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | BE73 |
| Product key | BE7321 |
| GTIN | 4046356457866 |
| Weight per piece (including packing) | 82.14 g |
| Weight per piece (excluding packing) | 82.14 g |
| Customs tariff number | 85369010 |
| Country of origin | AT |

3240181

<https://www.phoenixcontact.com/us/products/3240181>

Technical data

Product properties

| | |
|-----------------------|------------------|
| Product type | Europe connector |
| Number of positions | 12 |
| Pitch | 15 mm |
| Number of connections | 24 |
| Number of rows | 1 |

Electrical properties

| | |
|---|--------|
| Maximum power dissipation for nominal condition | 2.43 W |
|---|--------|

Connection data

| | |
|---|--|
| Nominal cross section | 16 mm ² |
| Connection method | Screw connection |
| Screw thread | M4 |
| Tightening torque | 1.2 ... 1.5 Nm |
| Stripping length | 8 mm |
| Conductor cross-section rigid | 1.5 mm ² ... 16 mm ² |
| Cross section AWG | 14 ... 6 (converted acc. to IEC) |
| Conductor cross-section flexible | 2.5 mm ² ... 16 mm ² |
| Conductor cross-section, flexible [AWG] | 14 ... 6 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 1.5 mm ² ... 10 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 1.5 mm ² ... 10 mm ² |
| 2 conductors with same cross section, rigid | 1.5 mm ² ... 4 mm ² |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve | 1.5 mm ² ... 2.5 mm ² |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.75 mm ² ... 2.5 mm ² |
| Nominal cross section | 16 mm ² |
| Nominal current | 76 A (with 16 mm ² conductor cross-section) |
| Maximum load current | 76 A (with 16 mm ² conductor cross-section) |
| Nominal voltage | 450 V |

Dimensions

| | |
|--------------------|---------|
| Width | 25.2 mm |
| Height | 20.8 mm |
| Depth | 25.2 mm |
| Drill hole spacing | 15 mm |
| Pitch | 15 mm |

Material specifications

| | |
|--|-------------|
| Color | transparent |
| Flammability rating according to UL 94 | V2 |

EC 16 TR - Europe connectors



3240181

<https://www.phoenixcontact.com/us/products/3240181>

| | |
|---------------------|----|
| Insulating material | PA |
|---------------------|----|

Mechanical properties

Mechanical data

| | |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

Technical data

| | |
|--------------------|-------|
| Drill hole spacing | 15 mm |
|--------------------|-------|

Mounting

| | |
|---------------|-------------------------|
| Mounting type | direct screw connection |
|---------------|-------------------------|

EC 16 TR - Europe connectors

3240181

<https://www.phoenixcontact.com/us/products/3240181>



Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

EC 16 TR - Europe connectors



3240181

<https://www.phoenixcontact.com/us/products/3240181>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | b8d11979-face-410b-a9af-767b5bd33f5d |

EF3.1 Climate Change

| | |
|---------|--------------|
| CO2e kg | 0.14 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com