

AI 0,34-8 TQ-B - Ferrule

3240249

<https://www.phoenixcontact.com/us/products/3240249>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Ferrules, taped, 0.34 mm², sleeve length: 8 mm, color: turquoise (CF 3000-TOOLKIT 0,25 is required)



Your advantages

- The taped ferrules were developed specifically for the CF 3000-2,5 automatic crimping device
- Available in the main color ranges up to 2.5 mm²
- Can be used to wire all terminal blocks, especially those of the CLIPLINE complete system

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3240249 |
| Packing unit | 1,000 pc |
| Minimum order quantity | 1,000 pc |
| Sales key | BH34 |
| Product key | BH3414 |
| GTIN | 4046356461405 |
| Weight per piece (including packing) | 0.095 g |
| Weight per piece (excluding packing) | 0.095 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

AI 0,34-8 TQ-B - Ferrule

3240249

<https://www.phoenixcontact.com/us/products/3240249>

Technical data

Product properties


| | |
|------------------|--|
| Product type | Cable end sleeve |
| Product property | Taped design for automated production |
| | UL certified |
| | Made from soft tin-plated electrolytic copper |
| | Correspond to the requirements of DIN 46228-4 and UL 486F in terms of size |
| | Plastic collar made of polypropylene |
| | Halogen-free |
| | Long/short-term temperature: +105°C/+120°C |

Connection data

Conductor connection

| | |
|---------------------------------------|----------------------|
| Conductor cross-section flexible max. | 0.34 mm ² |
| Conductor cross-section AWG max. | 22 |
| Stripping length | 10 mm |

Dimensions

| | |
|---|--|
| Dimensional drawing |  |
| Sleeve length | 12.5 mm |
| Length contact range | 8 mm |
| Maximum stripping length | 10 mm |
| Ferrule diameter | 0.8 mm |
| Sleeve wall thickness | 0.15 mm |
| Insulating collar thickness | 0.25 mm |
| Inner dimensions of the insulating collar | 2.2 mm |

Material specifications

| | |
|--|--------------------------------|
| Color | pastel turquoise (RAL 6034) |
| Material | CU-DHP |
| Flammability rating according to UL 94 | HB |
| Coating | galvanically tin-plated |
| Surface characteristics | Tin-plated |
| Components | free from silicone and halogen |

Mechanical properties

Technical data

AI 0,34-8 TQ-B - Ferrule



3240249

<https://www.phoenixcontact.com/us/products/3240249>

| | |
|---------------|---------|
| Sleeve length | 12.5 mm |
|---------------|---------|

Environmental and real-life conditions

Ambient conditions

| | |
|------------------------|---|
| Permanent temperature | 105 °C (-40 °C no load / 0 °C dynamic load) |
| Short-term temperature | 120 °C |

Standards and regulations

| | |
|------------------------------|------------------------|
| Design according to standard | UL 486F-E, Sonderfarbe |
|------------------------------|------------------------|

Drawings

Dimensional drawing



Sleeve length (b), length contact range (h), insulating collar inner dimension (d), sleeve diameter (k), insulating collar thickness (i), sleeve wall thickness (j)

AI 0,34-8 TQ-B - Ferrule



3240249

<https://www.phoenixcontact.com/us/products/3240249>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240249>



cULus Listed

Approval ID: E488001

AI 0,34-8 TQ-B - Ferrule



3240249

<https://www.phoenixcontact.com/us/products/3240249>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27400201 |
| ECLASS-15.0 | 27400201 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000005 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27121700 |
|-------------|----------|

AI 0,34-8 TQ-B - Ferrule



3240249

<https://www.phoenixcontact.com/us/products/3240249>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.002 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com