

WT-HF 4,5X200 - Cable tie

3240760

<https://www.phoenixcontact.com/us/products/3240760>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable binders for quick and secure bundling, standard version

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3240760 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | BE07 |
| Product key | BE7131 |
| GTIN | 4046356704786 |
| Weight per piece (including packing) | 1.301 g |
| Weight per piece (excluding packing) | 1.301 g |
| Customs tariff number | 39269097 |
| Country of origin | IT |

WT-HF 4,5X200 - Cable tie



3240760

<https://www.phoenixcontact.com/us/products/3240760>

Technical data

Product properties

| | |
|----------------------|-----------|
| Product type | Cable tie |
| Tensile strength GRP | 220 N |

Dimensions

| | |
|--------|--------|
| Width | 4.8 mm |
| Length | 200 mm |

Material specifications

| | |
|--|--------------------------------|
| RoHS compliant | yes |
| Color | transparent |
| Material | PA 6.6 |
| Flammability rating according to UL 94 | V2 |
| Components | free from silicone and halogen |

Cable/line

| | |
|-------------------------|----------------|
| External cable diameter | 3 mm ... 50 mm |
| Tensile strength | 220 N |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Optimum ambient temperature (storage/transport) | 23.00 °C 50.00 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat. |
| Ambient temperature (operation) | -40 °C ... 85 °C |
| Ambient temperature (assembly) | -10 °C ... 60 °C |
| Resistance to UV radiation | no |
| Short-term temperature | 110 °C |
| Recommended storage conditions | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |

Mounting

| | |
|---------------|-------------------|
| Mounting type | Cannot be removed |
|---------------|-------------------|

WT-HF 4,5X200 - Cable tie

3240760

<https://www.phoenixcontact.com/us/products/3240760>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240760>

DNV

Approval ID: TAE00004VK



UL Recognized

Approval ID: E328576-20210901

WT-HF 4,5X200 - Cable tie

3240760

<https://www.phoenixcontact.com/us/products/3240760>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-15.0 | 27140702 |
| ECLASS-13.0 | 27140702 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000046 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

WT-HF 4,5X200 - Cable tie

3240760

<https://www.phoenixcontact.com/us/products/3240760>



Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com