

WT-STEEL SH 7,9X838 - Cable tie



3240766

<https://www.phoenixcontact.com/us/products/3240766>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable binders, made from rust-free stainless steel (AISI 316), suitable for the harshest of ambient conditions (for example, salt water), with ball lock, for quick and secure bundling and fastening

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3240766 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | BE07 |
| Product key | BE7132 |
| GTIN | 4046356704847 |
| Weight per piece (including packing) | 15.56 g |
| Weight per piece (excluding packing) | 15.56 g |
| Customs tariff number | 73269098 |
| Country of origin | GB |

Technical data

Product properties

| | |
|----------------------|-----------|
| Product type | Cable tie |
| Tensile strength GRP | 1335 N |

Dimensions

| | |
|-------------------------|---------|
| Width | 7.9 mm |
| Length | 838 mm |
| Max. material thickness | 0.25 mm |

Material specifications

| | |
|----------------|---------------------------------|
| RoHS compliant | yes |
| Color | silver-colored |
| Material | Stainless steel 1.4401/AISI 316 |
| Components | free from silicone and halogen |

Cable/line

| | |
|-------------------------|-------------|
| External cable diameter | ≤ 254.00 mm |
| Tensile strength | 1335 N |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|---|
| Ambient temperature (operation) | -80 °C ... 538 °C |
| Ambient temperature (assembly) | -80 °C ... 538 °C |
| Resistance to UV radiation | yes |
| Recommended storage conditions | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |

Mounting

| | |
|---------------|-------------------|
| Mounting type | Cannot be removed |
|---------------|-------------------|

WT-STEEL SH 7,9X838 - Cable tie



3240766

<https://www.phoenixcontact.com/us/products/3240766>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240766>



cULus Listed

Approval ID: E328576

DNV

Approval ID: TAE000057Y

WT-STEEL SH 7,9X838 - Cable tie



3240766

<https://www.phoenixcontact.com/us/products/3240766>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-15.0 | 27140702 |
| ECLASS-13.0 | 27140702 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000046 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

WT-STEEL SH 7,9X838 - Cable tie



3240766

<https://www.phoenixcontact.com/us/products/3240766>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.464 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com