

WT-HT HF 7,8X365 BK - Cable tie



3240793

<https://www.phoenixcontact.com/us/products/3240793>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable binders for quick and secure bundling, heat stabilized to 125°C (also up to 145°C for brief periods)

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3240793 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | BE07 |
| Product key | BE7131 |
| GTIN | 4046356705219 |
| Weight per piece (including packing) | 5.127 g |
| Weight per piece (excluding packing) | 5.2 g |
| Customs tariff number | 39269097 |
| Country of origin | HR |

WT-HT HF 7,8X365 BK - Cable tie



3240793

<https://www.phoenixcontact.com/us/products/3240793>

Technical data

Product properties

| | |
|----------------------|-----------|
| Product type | Cable tie |
| Tensile strength GRP | 540 N |

Dimensions

| | |
|--------|--------|
| Width | 7.8 mm |
| Length | 365 mm |

Material specifications

| | |
|--|--------------------------------|
| RoHS compliant | yes |
| Color | black (RAL 9005) |
| Material | PA 6.6 |
| Flammability rating according to UL 94 | V2 |
| Components | free from silicone and halogen |

Cable/line

| | |
|-------------------------|-----------------|
| External cable diameter | 8 mm ... 100 mm |
| Tensile strength | 540 N |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Optimum ambient temperature (storage/transport) | 23.00 °C 50.00 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat. |
| Ambient temperature (operation) | -40 °C ... 125 °C |
| Ambient temperature (assembly) | -10 °C ... 60 °C |
| Resistance to UV radiation | no |
| Short-term temperature | 145 °C |
| Recommended storage conditions | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |

Mounting

| | |
|---------------|-------------------|
| Mounting type | Cannot be removed |
|---------------|-------------------|

WT-HT HF 7,8X365 BK - Cable tie



3240793

<https://www.phoenixcontact.com/us/products/3240793>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27140702 |
| ECLASS-15.0 | 27140702 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000046 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

WT-HT HF 7,8X365 BK - Cable tie



3240793

<https://www.phoenixcontact.com/us/products/3240793>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com