

# WP-SC PA HF 28,5 BK - Cable protection end sleeve



3240985

<https://www.phoenixcontact.com/us/products/3240985>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable protection end sleeve, material: PA 6, color: black, flammability rating in acc. with UL 94: V2, inside diameter: 20.8 mm

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3240985       |
| Packing unit                         | 25 pc         |
| Minimum order quantity               | 25 pc         |
| Sales key                            | BF68          |
| Product key                          | AF7DSA        |
| GTIN                                 | 4046356711036 |
| Weight per piece (including packing) | 4.256 g       |
| Weight per piece (excluding packing) | 3.294 g       |
| Customs tariff number                | 39174000      |
| Country of origin                    | DE            |

# WP-SC PA HF 28,5 BK - Cable protection end sleeve



3240985

<https://www.phoenixcontact.com/us/products/3240985>

## Technical data

### Product properties

|              |                |
|--------------|----------------|
| Product type | Protective cap |
|--------------|----------------|

### Dimensions

|          |         |
|----------|---------|
| Length   | 22 mm   |
| Diameter | 28.5 mm |

### Internal dimensions

|                   |         |
|-------------------|---------|
| Internal diameter | 20.8 mm |
|-------------------|---------|

### Material specifications

|  |              |
|--|--------------|
| Material                               | PA 6         |
| Flammability rating according to UL 94 | V2           |
| Components                             | halogen-free |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
|---------------------------------|-------------------|

# WP-SC PA HF 28,5 BK - Cable protection end sleeve



3240985

<https://www.phoenixcontact.com/us/products/3240985>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240985>



**UL Recognized**  
Approval ID: E86359



LR

3240985

<https://www.phoenixcontact.com/us/products/3240985>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-15.0 | 27430316 |
| ECLASS-13.0 | 27430316 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000519 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

3240985

<https://www.phoenixcontact.com/us/products/3240985>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.386 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)