


PTIO 1,5/S/4-LED 24 GN - Initiator/actuator terminal block



3244520

<https://www.phoenixcontact.com/us/products/3244520>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Initiator/actuator terminal block, with green light indicator, nom. voltage: 250 V, nominal current: 13.5 A, number of connections: 5, connection method: Push-in connection, Rated cross section: 1.5 mm², cross section: 0.14 mm² - 1.5 mm², mounting type: NS 35/7,5, NS 35/15, color: gray

Your advantages

- The Push-in connection terminal blocks are characterized by the system features of the CLIPLINE complete system and by easy and tool-free wiring of conductors with ferrules or solid conductors
- The compact design and front connection enable wiring in a confined space

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3244520 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BE22 |
| Product key | BE2218 |
| GTIN | 4046356735926 |
| Weight per piece (including packing) | 8.52 g |
| Weight per piece (excluding packing) | 8.52 g |
| Customs tariff number | 85369010 |
| Country of origin | PL |

PTIO 1,5/S/4-LED 24 GN - Initiator/actuator terminal block



3244520

<https://www.phoenixcontact.com/us/products/3244520>

Technical data

Notes

General

| | |
|------|---|
| Note | Current and voltage are determined by the resistance and the light indicator. |
|------|---|

Product properties

| | |
|-----------------------|--------------------------------|
| Product type | Sensor/actuator terminal block |
| Number of connections | 5 |
| Number of rows | 4 |
| Potentials | 4 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|---------------------|---------------------------|
| Rated surge voltage | 4 kV |
| LED voltage range | 15 V AC/DC ... 30 V AC/DC |
| LED current range | 0.31 mA ... 0.95 mA |

Input data

| | |
|-------------------|---------------------------|
| LED voltage range | 15 V AC/DC ... 30 V AC/DC |
|-------------------|---------------------------|

Connection data

| | |
|---|--|
| Number of connections per level | 2 |
| Nominal cross section | 1.5 mm ² |
| Connection method | Push-in connection |
| Stripping length | 8 mm ... 10 mm |
| Internal cylindrical gage | A1 / B1 |
| Connection in acc. with standard | IEC 60947-7-1 |
| Conductor cross-section rigid | 0.14 mm ² ... 1.5 mm ² |
| Cross section AWG | 26 ... 16 (converted acc. to IEC) |
| Conductor cross-section flexible | 0.14 mm ² ... 1.5 mm ² |
| Conductor cross-section, flexible [AWG] | 26 ... 16 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.14 mm ² ... 1.5 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.14 mm ² ... 1 mm ² (Using the AI-S 1-8 TQ ferrule, Item No. 1200293, is recommended) |
| Nominal cross section | 1.5 mm ² |
| Nominal current | 13.5 A |
| Maximum load current | 13.5 A |
| Nominal voltage | 250 V |

Connection cross sections directly pluggable

PTIO 1,5/S/4-LED 24 GN - Initiator/actuator terminal block



3244520

<https://www.phoenixcontact.com/us/products/3244520>

| | |
|---|--|
| Conductor cross-section rigid | 0.25 mm ² ... 1.5 mm ² |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.34 mm ² ... 1.5 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.34 mm ² ... 1 mm ² |

Dimensions

| | |
|--------------------|---------|
| Width | 3.5 mm |
| End cover width | 2.2 mm |
| Height | 90.8 mm |
| Depth | 40 mm |
| Depth on NS 35/7,5 | 41.5 mm |
| Depth on NS 35/15 | 48.5 mm |

Material specifications

| | |
|---|-----------------|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 | V0 |
| Insulating material group | I |
| Insulating material | PA |
| Static insulating material application in cold | -60 °C |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Calorimetric heat release NFPA 130 (ASTM E 1354) | 28 MJ/kg |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Mechanical properties

Mechanical data

| | |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

Environmental and real-life conditions

Ambient conditions

| | |
|--|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

PTIO 1,5/S/4-LED 24 GN - Initiator/actuator terminal block



3244520

<https://www.phoenixcontact.com/us/products/3244520>

Standards and regulations

| | |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

Mounting

| | |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
| | NS 35/15 |

PTIO 1,5/S/4-LED 24 GN - Initiator/actuator terminal block




3244520


<https://www.phoenixcontact.com/us/products/3244520>


Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3244520>

|  CSA Approval ID: 13631 | | | | |
|--|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| B | 300 V | 10 A | 26 - 14 | - |
| C | 150 V | 15 A | 26 - 14 | - |
| D | 300 V | 10 A | 26 - 14 | - |

|  EAC Approval ID: RU C-DE.BL08.B.00644 | | | | |
|---|--|--|--|--|
|---|--|--|--|--|

|  cULus Recognized Approval ID: E60425 | | | | |
|--|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| B | 300 V | 15 A | 26 - 14 | - |
| C | 150 V | 15 A | 26 - 14 | - |
| D | 300 V | 10 A | 26 - 14 | - |

|  EAC Approval ID: KZ7500651131219505 | | | | |
|---|--|--|--|--|
|---|--|--|--|--|

PTIO 1,5/S/4-LED 24 GN - Initiator/actuator terminal block



3244520

<https://www.phoenixcontact.com/us/products/3244520>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250112 |
| ECLASS-15.0 | 27250112 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000900 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

PTIO 1,5/S/4-LED 24 GN - Initiator/actuator terminal block



3244520

<https://www.phoenixcontact.com/us/products/3244520>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com