# PTFIX-NS35 - DIN rail adapter

3274054

https://www.phoenixcontact.com/us/products/3274054

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail adapter, for NS 35 and NS 15 for accommodating 2.5 mm$^2$, 4 mm$^2$, and 10 mm$^2$ FIX blocks in vertical direction, color: gray



## Commercial data

| | |
|---|---|
| Item number | 3274054 |
| Packing unit | 20 pc |
| Minimum order quantity | 20 pc |
| Sales key | BE09 |
| Product key | BEAZ11 |
| GTIN | 4055626377162 |
| Weight per piece (including packing) | 4.66 g |
| Weight per piece (excluding packing) | 4.515 g |
| Customs tariff number | 39269097 |
| Country of origin | PL |

## Technical data

### Notes

| | |
|---|---|
| Assembly note | for NS 35 and NS 15 for accommodating 2.5 mm², 4 mm², and 10 mm² FIX blocks in the vertical direction |

### Product properties

| | |
|---|---|
| Product type | Mounting material |

### Dimensions

| | |
|---|---|
| Width | 28.6 mm |
| Height | 58.1 mm |
| Depth | 11 mm |
| Depth on NS 35/7,5 | 15 mm |
| Depth on NS 35/15 | 22.5 mm |

### Material specifications

| | |
|---|---|
| Color | gray (RAL 7042) |
| Material | PA |
| Flammability rating according to UL 94 | V0 |

### Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

### Mounting

| | |
|---|---|
| Mounting type | NS 35/7,5 |
| | NS 35/15 |
| | NS 15 |

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27370419 |
| ECLASS-15.0 | 27370419 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC001024 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121400 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

EF3.1 Climate Change

| | |
|---|---|
| CO2e kg | 0.033 kg CO2e |


Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com



Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com