


RBO 10 - Bolt connection terminal block



3244614

<https://www.phoenixcontact.com/us/products/3244614>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bolt connection terminal block, nom. voltage: 1000 V, nominal current: 309 A, number of connections: 2, number of positions: 1, connection method: Bolt connection, Rated cross section: 150 mm², mounting type: NS 35/7,5, NS 35/15, color: gray

Your advantages

- Tested for railway applications

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3244614 |
| Packing unit | 5 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE44 |
| Product key | BE4412 |
| GTIN | 4046356583947 |
| Weight per piece (including packing) | 274 g |
| Weight per piece (excluding packing) | 252.96 g |
| Customs tariff number | 85369010 |
| Country of origin | IN |

RBO 10 - Bolt connection terminal block



3244614

<https://www.phoenixcontact.com/us/products/3244614>

Technical data

Product properties

| | |
|-----------------------|--------------------------------|
| Product type | Bolt connection terminal block |
| Product family | RBO |
| Area of application | Railway industry |
| | Machine building |
| | Plant engineering |
| Number of positions | 1 |
| Pitch | 41 mm |
| Number of connections | 2 |
| Number of rows | 1 |
| Potentials | 1 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|---|--------|
| Rated surge voltage | 8 kV |
| Maximum power dissipation for nominal condition | 9.55 W |

Connection data

| | |
|----------------------------------|---|
| Number of connections per level | 2 |
| Nominal cross section | 150 mm ² |
| Connection method | Bolt connection |
| Screw thread | M10 |
| Stripping length | The stripping length depends on the specification provided by the cable lug manufacturer. |
| Connection in acc. with standard | IEC 60947-7-1 |
| Nominal cross section | 150 mm ² |
| Nominal current | 309 A |
| Maximum load current | 309 A (with 150 mm ² conductor cross-section) |
| Nominal voltage | 1000 V |

Cable lug connection DIN 46234:1980-03

| | |
|----------------------------------|---|
| Connection in acc. with standard | DIN 46234:1980-03 |
| Cross section | 6 mm ² ... 150 mm ² |
| Cross section range AWG | (converted acc. to IEC) |
| Hole diameter | 10.5 mm |
| Width | 30 mm |
| Bolt diameter | 10 mm |
| Screw thread | M10 |
| Tightening torque | 10 ... 20 Nm |
| Connection in acc. with standard | DIN 46235:1983-07 |

RBO 10 - Bolt connection terminal block



3244614

<https://www.phoenixcontact.com/us/products/3244614>

| | |
|--|--|
| Cross section | 16 mm ² ... 150 mm ² |
| Cross section range AWG | (converted acc. to IEC) |
| Hole diameter | 10.5 mm |
| Width | 34 mm |
| Bolt diameter | 10 mm |
| Screw thread | M10 |
| Tightening torque | 10 ... 20 Nm |
| Connection in acc. with standard | DIN 46237:1970-07 |
| Cross section | 6 mm ² ... 6 mm ² |
| Cross section range AWG | (converted acc. to IEC) |
| Hole diameter | 10.5 mm |
| Width | 18 mm |
| Bolt diameter | 10 mm |
| Screw thread | M10 |
| Tightening torque | 10 ... 20 Nm |
| Identification color of ring cable lugs : yellow | 6 mm ² |

Ex data

Rated data (ATEX/IECEx)

| | |
|-----------------------------|--|
| Identification | ⊕ II 2 GD Ex eb IIC Gb |
| Operating temperature range | -60 °C ... 110 °C |
| Ex-certified accessories | 3247970 HC-RBO 10 0800886 E/NS 35 N |
| List of bridges | / RBO 10-VS 2 / 3244643 / RBO 10-VS 3 / 3244656 |
| Bridge data | 309 A (150 mm ²) |
| Ex temperature increase | 40 K (309 A / 150 mm ²) |
| for bridging with bridge | 1100 V |
| Rated insulation voltage | 1000 V |
| output | (Permanent) |

Ex level General

| | |
|----------------------|---------|
| Rated voltage | 1100 V |
| Rated current | 309 A |
| Maximum load current | 309 A |
| Contact resistance | 0.05 mΩ |

Ex connection data General

| | |
|------------------------------|---|
| Torque range | 10 Nm ... 20 Nm |
| Nominal cross section | 150 mm ² |
| Rated cross section AWG | 300 kcmil |
| Connection capacity rigid | 6 mm ² ... 150 mm ² |
| Connection capacity AWG | 10 ... 300 kcmil |
| Connection capacity flexible | 6 mm ² ... 150 mm ² |

RBO 10 - Bolt connection terminal block




3244614

<https://www.phoenixcontact.com/us/products/3244614>

| | |
|---|---|
| Connection capacity AWG | 10 ... 300 kcmil |
| 2 conductors with same cross section, solid | 6 mm ² ... 150 mm ² |
| 2 conductors with the same cross-section AWG rigid | 10 ... 300 kcmil |
| 2 conductors with same cross section, stranded | 6 mm ² ... 150 mm ² |
| 2 conductors with the same cross-section AWG flexible | 10 ... 300 kcmil |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 41 mm |
| Height | 144 mm |
| Depth on NS 35/7,5 | 77 mm |
| Depth on NS 35/15 | 84.5 mm |
| Bolt length | 31 mm |
| Hole diameter | 6.4 mm |
| Pitch | 41 mm |

Material specifications

| | |
|--|-----------------|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 | V0 |
| Insulating material group | I |
| Insulating material | PA |
| Static insulating material application in cold | -60 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Electrical tests

Surge voltage test

| | |
|-----------------------|-------------|
| Test voltage setpoint | 9.8 kV |
| Result | Test passed |

Temperature-rise test

RBO 10 - Bolt connection terminal block



3244614

<https://www.phoenixcontact.com/us/products/3244614>

| | |
|--|-------------------------------------|
| Requirement temperature-rise test | Increase in temperature ≤ 45 K |
| Result | Test passed |
| | Test passed |
| Short-time withstand current 150 mm ² | 18 kA |
| Result | Test passed |

Power-frequency withstand voltage

| | |
|-----------------------|-------------|
| Test voltage setpoint | 2.2 kV |
| Result | Test passed |

Mechanical properties

Mechanical data

| | |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

Mechanical tests

Mechanical strength

| | |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

Attachment on the carrier

| | |
|---------------------|-------------|
| Test force setpoint | 15 N |
| Result | Test passed |

Test for conductor damage and slackening

| | |
|--------------------------------|-----------------------------|
| Rotation speed | 10 (+/- 2) rpm |
| Revolutions | 135 |
| Conductor cross-section/weight | 150 mm ² / 15 kg |
| Result | Test passed |

Environmental and real-life conditions

Needle-flame test

| | |
|------------------|-------------|
| Time of exposure | 30 s |
| Result | Test passed |

Oscillation/broadband noise

| | |
|------------------------|---|
| Specification | DIN EN 50155 (VDE 0115-200):2022-06 |
| Spectrum | Long life test category 2, bogie-mounted |
| Frequency | $f_1 = 5$ Hz to $f_2 = 250$ Hz |
| ASD level | 6.12 (m/s ²) ² /Hz |
| Acceleration | 3.12g |
| Test duration per axis | 5 h |
| Test directions | X-, Y- and Z-axis |
| Result | Test passed |

Shocks

| | |
|---------------|-------------------------------------|
| Specification | DIN EN 50155 (VDE 0115-200):2008-03 |
|---------------|-------------------------------------|

RBO 10 - Bolt connection terminal block



3244614

<https://www.phoenixcontact.com/us/products/3244614>

| | |
|--------------------------------|-----------------------------------|
| Pulse shape | Half-sine |
| Acceleration | 5g |
| Shock duration | 30 ms |
| Number of shocks per direction | 3 |
| Test directions | X-, Y- and Z-axis (pos. and neg.) |
| Result | Test passed |

Ambient conditions

| | |
|--|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Standards and regulations

| | |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

Mounting

| | |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
| | NS 35/15 |

RBO 10 - Bolt connection terminal block




3244614

<https://www.phoenixcontact.com/us/products/3244614>

Drawings

Dimensional drawing



RBO 10 - Bolt connection terminal block



3244614

<https://www.phoenixcontact.com/us/products/3244614>

Circuit diagram



RBO 10 - Bolt connection terminal block





3244614

<https://www.phoenixcontact.com/us/products/3244614>


Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3244614>


|  CSA Approval ID: 13631 | | | | |
|--|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| B | 600 V | 310 A | 10 - 350 | - |
| C | 1000 V | 310 A | 10 - 350 | - |
| E | 600 V | 310 A | 10 - 350 | - |

|  UL Recognized Approval ID: E60425 | | | | |
|---|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| B | 600 V | 310 A | 10 - 350 | - |
| C | 600 V | 310 A | 10 - 350 | - |
| E | 1000 V | 310 A | 10 - 350 | - |

| DNV Approval ID: TAE00004G1 | | | | |
|---------------------------------------|--|--|--|--|
|---------------------------------------|--|--|--|--|

|  EAC Ex Approval ID: KZ 7500525010101950 | | | | |
|---|--|--|--|--|
|---|--|--|--|--|

|  IECEX Approval ID: IECEXSEV13.0003U | | | | |
|---|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | 1100 V | 309 A | - | 6 - 150 |

|  ATEX Approval ID: SEV13ATEX0132U | | | | |
|--|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | 1100 V | 309 A | - | 6 - 150 |

RBO 10 - Bolt connection terminal block



3244614

<https://www.phoenixcontact.com/us/products/3244614>



CCC

Approval ID: 2020322313000627



UKCA-EX

Approval ID: CML 22UKEX1230U

RBO 10 - Bolt connection terminal block



3244614

<https://www.phoenixcontact.com/us/products/3244614>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250101 |
| ECLASS-15.0 | 27250101 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000897 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

RBO 10 - Bolt connection terminal block



3244614

<https://www.phoenixcontact.com/us/products/3244614>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com