


UTN 16 - N disconnect terminal block

3245053

<https://www.phoenixcontact.com/us/products/3245053>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



N disconnect terminal block, **Assembly instruction:**

In order to securely fix the neutral busbar in place, support brackets must be placed at the beginning and end of each terminal strip as well as every 20 cm on longer terminal strips.

The corresponding support brackets can be found at [phoenixcontact.com/products](https://www.phoenixcontact.com/products), for neutral conductor disconnection, nom. voltage: 400 V, nominal current: 76 A, Screw connection, Rated cross section: 16 mm², cross section: 6 mm² - 25 mm², mounting type: NS 35/7,5, NS 35/15, color: blue

Your advantages

- Same shape as UT standard terminal blocks

Commercial data

Item number	3245053
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE01
Product key	BE1152
GTIN	4046356299008
Weight per piece (including packing)	31.32 g
Weight per piece (excluding packing)	31.32 g
Customs tariff number	85369010
Country of origin	PL

UTN 16 - N disconnect terminal block



3245053

<https://www.phoenixcontact.com/us/products/3245053>

Technical data

Product properties

Product type	Installation terminal block
Number of connections	2
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	2.43 W
Current carrying capacity of the neutral busbar	140 A

Connection data

Number of connections per level	2
Nominal cross section	16 mm ²

Level 1 above 1 below 1

Connection method	Screw connection
Screw thread	M5
Tightening torque	2.5 ... 3 Nm
Stripping length	12 mm
Internal cylindrical gage	B7
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	6 mm ² ... 25 mm ²
Cross section AWG	8 ... 4 (converted acc. to IEC)
Conductor cross-section flexible	6 mm ² ... 16 mm ²
Conductor cross-section, flexible [AWG]	8 ... 6 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	6 mm ² ... 16 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	6 mm ² ... 16 mm ²
2 conductors with same cross section, rigid	2.5 mm ² ... 10 mm ²
2 conductors with same cross section, flexible	2.5 mm ² ... 6 mm ²
2 conductors with same cross section, flexible, with ferrule without plastic sleeve	4 mm ² ... 6 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	4 mm ² ... 6 mm ²
Nominal cross section	16 mm ²
Nominal current	76 A
Maximum load current	76 A
Nominal voltage	400 V

UTN 16 - N disconnect terminal block



3245053

<https://www.phoenixcontact.com/us/products/3245053>

Dimensions

Width	12.2 mm
Height	55 mm
Depth	49.9 mm
Depth on NS 35/7,5	50.5 mm
Depth on NS 35/15	58 mm

Material specifications

Color	blue (RAL 5015)
Flammability rating according to UL 94	V2
Insulating material group	I
Insulating material	PA
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	125 °C
Relative insulation material temperature index (Elec., UL 746 B)	125 °C

Electrical tests

Surge voltage test

Test voltage setpoint	4.8 kV
Result	Test passed

Temperature-rise test

Requirement temperature-rise test	Increase in temperature ≤ 45 K
Result	Test passed
Short-time withstand current 16 mm ²	1.92 kA
Result	Test passed

Power-frequency withstand voltage

Test voltage setpoint	1.5 kV
Result	Test passed

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Mechanical tests

Mechanical strength

Result	Test passed
--------	-------------

Attachment on the carrier

DIN rail/fixing support	NS 35
Test force setpoint	5 N
Result	Test passed

UTN 16 - N disconnect terminal block



3245053

<https://www.phoenixcontact.com/us/products/3245053>

Test for conductor damage and slackening

Rotation speed	10 rpm
Revolutions	135
Conductor cross-section/weight	6 mm ² / 1.4 kg
	16 mm ² / 2.9 kg
	25 mm ² / 4.5 kg
Result	Test passed

Environmental and real-life conditions

Aging

Temperature cycles	192
Result	Test passed

Needle-flame test

Time of exposure	30 s
Result	Test passed

Oscillation/broadband noise

Specification	DIN EN 50155 (VDE 0115-200):2008-03
Spectrum	Long life test category 1, class B, body mounted
Frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$
ASD level	1.857 (m/s ²)/Hz
Acceleration	0.8g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Result	Test passed

Shocks

Specification	DIN EN 50155 (VDE 0115-200):2008-03
Acceleration	5g
Shock duration	30 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

UTN 16 - N disconnect terminal block



3245053

<https://www.phoenixcontact.com/us/products/3245053>

Mounting

Mounting type	NS 35/7,5
	NS 35/15

UTN 16 - N disconnect terminal block

3245053

<https://www.phoenixcontact.com/us/products/3245053>



Drawings

Circuit diagram



UTN 16 - N disconnect terminal block



3245053

<https://www.phoenixcontact.com/us/products/3245053>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3245053>



EAC

Approval ID: KZ7500651131219505

UTN 16 - N disconnect terminal block



3245053

<https://www.phoenixcontact.com/us/products/3245053>

Classifications

ECLASS

ECLASS-13.0	27250111
ECLASS-15.0	27250111

ETIM

ETIM 10.0	EC001257
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UTN 16 - N disconnect terminal block



3245053

<https://www.phoenixcontact.com/us/products/3245053>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.426 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com