

UTN 35 - N disconnect terminal block



3245066

<https://www.phoenixcontact.com/us/products/3245066>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



N disconnect terminal block, **Assembly instructions:**

For secure fastening of the neutral busbar, supports must be set at the beginning and end of each terminal strip as well as every 20 cm on longer terminal strips., for neutral conductor disconnection, nom. voltage: 400 V, nominal current: 110 A, Special and hybrid connection, 1st level connection right, Rated cross section: 35 mm², cross section: 0.75 mm² - 35 mm², mounting type: NS 35/7,5, NS 35/15, color: blue

Your advantages

- Same shape as UT standard terminal blocks

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3245066 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BE01 |
| Product key | BE1152 |
| GTIN | 4046356299039 |
| Weight per piece (including packing) | 48.376 g |
| Weight per piece (excluding packing) | 46.93 g |
| Customs tariff number | 85369010 |
| Country of origin | TR |

UTN 35 - N disconnect terminal block



3245066

<https://www.phoenixcontact.com/us/products/3245066>

Technical data

Notes

General

| | |
|------|--|
| Note | The max. load current must not be exceeded by the total current of all connected conductors. |
|------|--|

Product properties

| | |
|-----------------------|-----------------------------|
| Product type | Installation terminal block |
| Number of connections | 2 |
| Number of rows | 1 |
| Potentials | 1 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|---|--------|
| Rated surge voltage | 6 kV |
| Maximum power dissipation for nominal condition | 4.06 W |
| Current carrying capacity of the neutral busbar | 140 A |

Connection data

| | |
|------------------------------------|--------------------|
| Number of connections per level | 2 |
| Nominal cross section | 35 mm ² |
| Tightening torque disconnect slide | M5 2.5 ... 3 Nm |

1st level connection right

| | |
|---|---|
| Connection method | Special and hybrid connection |
| Screw thread | M6 |
| Tightening torque | 3.2 ... 3.7 Nm |
| Stripping length | 16 mm |
| Connection in acc. with standard | IEC 60947-7-1 |
| Conductor cross-section rigid | 0.75 mm ² ... 35 mm ² |
| Cross section AWG | 18 ... 2 (converted acc. to IEC) |
| Conductor cross-section flexible | 0.75 mm ² ... 35 mm ² |
| Conductor cross-section, flexible [AWG] | 18 ... 2 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.75 mm ² ... 35 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.75 mm ² ... 35 mm ² |
| 2 conductors with same cross section, rigid | 0.75 mm ² ... 10 mm ² |
| 2 conductors with same cross section, flexible | 0.75 mm ² ... 10 mm ² |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve | 0.75 mm ² ... 10 mm ² |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.75 mm ² ... 6 mm ² |

UTN 35 - N disconnect terminal block



3245066

<https://www.phoenixcontact.com/us/products/3245066>

| | |
|-----------------------|---|
| Nominal cross section | 35 mm ² |
| Nominal current | 110 A |
| Maximum load current | 110 A (with 35 mm ² conductor cross-section) |
| Nominal voltage | 400 V |

Dimensions

| | |
|--------------------|---------|
| Width | 15 mm |
| Height | 55 mm |
| Depth | 49.8 mm |
| Depth on NS 32 | 56 mm |
| Depth on NS 35/7,5 | 51 mm |

Material specifications

| | |
|---|-----------------|
| Color | blue (RAL 5015) |
| Flammability rating according to UL 94 | V2 |
| Insulating material group | I |
| Insulating material | PA |
| Static insulating material application in cold | -40 °C |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 125 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 125 °C |

Electrical tests

Surge voltage test

| | |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

Temperature-rise test

| | |
|---|--------------------------------|
| Requirement temperature-rise test | Increase in temperature ≤ 45 K |
| Result | Test passed |
| Short-time withstand current 35 mm ² | 4.2 kA |
| Result | Test passed |

Power-frequency withstand voltage

| | |
|-----------------------|-------------|
| Test voltage setpoint | 1.89 kV |
| Result | Test passed |

Mechanical properties

Mechanical data

| | |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

Mechanical tests

Mechanical strength

| | |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

Test for conductor damage and slackening

UTN 35 - N disconnect terminal block



3245066

<https://www.phoenixcontact.com/us/products/3245066>

| | |
|--------------------------------|-------------------------------|
| Rotation speed | 10 (+/- 2) rpm |
| Revolutions | 135 |
| Conductor cross-section/weight | 0.75 mm ² / 0.4 kg |
| | 10 mm ² / 2 kg |
| | 35 mm ² / 6.8 kg |
| Result | Test passed |

Environmental and real-life conditions

Needle-flame test

| | |
|------------------|-------------|
| Time of exposure | 30 s |
| Result | Test passed |

Oscillation/broadband noise

| | |
|------------------------|--|
| Specification | DIN EN 50155 (VDE 0115-200):2018-05 |
| Spectrum | Long life test category 2, bogie-mounted |
| Frequency | f ₁ = 5 Hz to f ₂ = 250 Hz |
| ASD level | 6.12 (m/s ²) ² /Hz |
| Acceleration | 3.12g |
| Test duration per axis | 5 h |
| Test directions | X-, Y- and Z-axis |
| Result | Test passed |

Shocks

| | |
|--------------------------------|-----------------------------------|
| Pulse shape | Semi-sinusoidal |
| Acceleration | 5g |
| Shock duration | 30 ms |
| Number of shocks per direction | 3 |
| Test directions | X-, Y- and Z-axis (pos. and neg.) |
| Result | Test passed |

Ambient conditions

| | |
|--|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Standards and regulations

| | |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

Mounting

| | |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
| | NS 35/15 |
| Screw thread | M5 |

UTN 35 - N disconnect terminal block

3245066

<https://www.phoenixcontact.com/us/products/3245066>



Drawings

Circuit diagram



UTN 35 - N disconnect terminal block



3245066

<https://www.phoenixcontact.com/us/products/3245066>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3245066>



EAC

Approval ID: KZ7500651131219505

UTN 35 - N disconnect terminal block



3245066

<https://www.phoenixcontact.com/us/products/3245066>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250111 |
| ECLASS-15.0 | 27250111 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001257 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

UTN 35 - N disconnect terminal block



3245066

<https://www.phoenixcontact.com/us/products/3245066>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.397 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com