


SSMK 60X18 - Control cabinet marker

5032439

<https://www.phoenixcontact.com/us/products/5032439>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Control cabinet marker, size: 60 x 18 mm, lettering field: 56 x 14 mm, 2 mounting holes M3, including 1 x ES-SSMK-GB 60 x 18

Your advantages

- The ES-SSMK ... insert strips can be labeled using the CMS-P1-PLOTTER and the CMS-P1-PAD magazine
- The labeling is resistant to external influences
- The base carrier has two fixing holes so that it can be screwed on
- Control cabinet markers consisting of a transparent cap and base carrier
- Once labeled, the insert label is inserted in the cap and this is then snapped onto the base carrier

Commercial data

Item number	5032439
Packing unit	50 pc
Minimum order quantity	1 pc
Sales key	BG18
Product key	BG241B
GTIN	4017918095802
Weight per piece (including packing)	4.636 g
Weight per piece (excluding packing)	4.636 g
Customs tariff number	39269097
Country of origin	PL

SSMK 60X18 - Control cabinet marker



5032439

<https://www.phoenixcontact.com/us/products/5032439>

Technical data

Product properties

Product type	Marker carriers
--------------	-----------------

Dimensions

Width	60.22 mm
Height	18.00 mm
Depth	4.50 mm

Text field

Text field width	56 mm
Text field height	14 mm

Material specifications

Color	multicolored (RAL -)
	white (RAL 9010)
	transparent
Flammability rating according to UL 94	V2
Base element material	PC
Components	free from silicone and halogen

Mechanical properties

Technical data

Drill hole spacing	40.00 mm
--------------------	----------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Mounting

Mounting type	screw, rivet
---------------	--------------

SSMK 60X18 - Control cabinet marker



5032439

<https://www.phoenixcontact.com/us/products/5032439>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

SSMK 60X18 - Control cabinet marker



5032439

<https://www.phoenixcontact.com/us/products/5032439>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com