

# BN-ZB 5/WH-100:UNBEDRUCKT - Marker pin Zack strip



5060964

<https://www.phoenixcontact.com/us/products/5060964>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker pin Zack strip, Strip, white (RAL 9010), unmarked, can be labeled with: CMS-P1-PLOTTER, mounting type: plug in, Number of individual labels: 1000, text field height: 4 mm, text field width: 4 mm

## Commercial data

Item number	5060964
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BG05
Product key	BG2112
GTIN	4017918096175
Weight per piece (including packing)	0.29 g
Weight per piece (excluding packing)	0.24 g
Customs tariff number	39269097
Country of origin	PL

# BN-ZB 5/WH-100:UNBEDRUCKT - Marker pin Zack strip



5060964

<https://www.phoenixcontact.com/us/products/5060964>

## Technical data

### Notes

General	Can be labeled with CMS
---------	-------------------------

### Product properties

Product type	Terminal marker
--------------	-----------------

### Marking

Number of individual labels	1000
Number of individual labels per row	10
Slot type	high
Identification technology	Plotter

### Dimensions

Width	4.00 mm
Height	3.97 mm
Depth	5.50 mm

### Text field

Text field width	4 mm
Text field height	4 mm

### Material specifications

Color	white (RAL 9010)
Flammability rating according to UL 94	V2
Base element material	PA
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
---------------	---------------------------------------

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

# BN-ZB 5/WH-100:UNBEDRUCKT - Marker pin Zack strip



5060964

<https://www.phoenixcontact.com/us/products/5060964>

## Mounting

Mounting type

plug in

# BN-ZB 5/WH-100:UNBEDRUCKT - Marker pin Zack strip



5060964

<https://www.phoenixcontact.com/us/products/5060964>

## Classifications

### ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

### ETIM

ETIM 10.0	EC000761
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# BN-ZB 5/WH-100:UNBEDRUCKT - Marker pin Zack strip



5060964

<https://www.phoenixcontact.com/us/products/5060964>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.004 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)