

# THERMOMARK CARD - Thermal transfer printer



5146464

<https://www.phoenixcontact.com/us/products/5146464>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

## Thermal transfer printer for cards



## Product description

The THERMOMARK CARD prints marking materials in card format for terminal marking, wire and cable marking, and equipment and plant marking to an incredibly high quality.

## Your advantages

- Maintenance-free operation with proven thermal transfer printer technology
- High-quality, fast labeling. Printing time for one UniCard: just 8 seconds.
- Easy operating concept based on user-friendly touch screen entry
- Easy to control with the PROJECT COMPLETE software

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 5146464                        |
| Packing unit                         | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | BG01                           |
| Product key                          | BG1221                         |
| GTIN                                 | 4046356528795                  |
| Weight per piece (including packing) | 9,820 g                        |
| Weight per piece (excluding packing) | 9,200 g                        |
| Customs tariff number                | 84433210                       |
| Country of origin                    | DE                             |

5146464

<https://www.phoenixcontact.com/us/products/5146464>

## Technical data

### Product properties

|              |                |
|--------------|----------------|
| Product type | Marking system |
|--------------|----------------|

### Marking

|                           |                |
|---------------------------|----------------|
| Identification technology | Thermotransfer |
|---------------------------|----------------|

### Device properties

|                  |   |
|------------------|---|
| Print width      | 104 mm  |
| Print resolution | 300 dpi   |
| Operating system | MS Windows Vista, MS Windows 7 (32/64-bit), MS Windows 8 (32/64-bit), MS Windows 8.1 (32/64-bit), MS Windows 10 (32/64-bit), Server 2008, Server 2008 R2, Server 2012, Server 2012 R2 |

### Electrical properties

#### Supply

|                      |   |
|----------------------|---|
| Supply voltage range | 100 V AC ... 240 V AC (50 Hz ... 60 Hz) |
|----------------------|---|

### Dimensions

|        |        |
|--------|--------|
| Width  | 254 mm |
| Height | 194 mm |
| Length | 325 mm |

### Material specifications

|       |      |
|-------|------|
| Color | gray |
|-------|------|

### Environmental and real-life conditions

#### Ambient conditions

|                                  |                |
|----------------------------------|----------------|
| Ambient temperature (operation)  | 5 °C ... 35 °C |
| Permissible humidity (operation) | 10 % ... 80 %  |

# THERMOMARK CARD - Thermal transfer printer



5146464

<https://www.phoenixcontact.com/us/products/5146464>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/5146464>



**IECEE CB Scheme**

Approval ID: DK-5443



**UL Listed**

Approval ID: E140403



**cUL Listed**

Approval ID: E140403



**KC**

Approval ID: KCC-REI-PCK-FL514646

5146464

<https://www.phoenixcontact.com/us/products/5146464>

## Environmental product compliance

### EU RoHS

|   |        |
|---|--------|
| Fulfills EU RoHS substance requirements | Yes    |
| Exemption                               | 7(c)-I |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)