

# THERMOMARK CARD SET PT PT - Thermal transfer printer set



5147219

<https://www.phoenixcontact.com/us/products/5147219>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

**Printing set**, consisting of: 1 x THERMOMARK CARD, Order No. 5146464, 1 x MARKING NOTEBOOK (without internal CD/DVD drive), CLIP-PROJECT PROFESSIONAL



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 5147219       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Product key                          | BG1222        |
| GTIN                                 | 4046356699822 |
| Weight per piece (including packing) | 999 g         |
| Weight per piece (excluding packing) | 999 g         |
| Country of origin                    | DE            |

# THERMOMARK CARD SET PT PT - Thermal transfer printer set



5147219

<https://www.phoenixcontact.com/us/products/5147219>

## Technical data

### Product properties

|              |                |
|--------------|----------------|
| Product type | Marking system |
|--------------|----------------|

### Marking

|                           |                |
|---------------------------|----------------|
| Identification technology | Thermotransfer |
|---------------------------|----------------|

### Device properties

|                  |   |
|------------------|---|
| Print width      | 104 mm                                      |
| Print resolution | 300 dpi                                     |
| Operating system | MS Windows 7, MS Windows 8.1, MS Windows 10 |

### Electrical properties

#### Supply

|                      |   |
|----------------------|---|
| Supply voltage range | 100 V AC ... 240 V AC (50 Hz ... 60 Hz) |
|----------------------|---|

### Dimensions

|        |        |
|--------|--------|
| Width  | 380 mm |
| Height | 189 mm |
| Length | 320 mm |

### Material specifications

|       |      |
|-------|------|
| Color | gray |
|-------|------|

### Environmental and real-life conditions

#### Ambient conditions

|                                  |                |
|----------------------------------|----------------|
| Ambient temperature (operation)  | 5 °C ... 35 °C |
| Permissible humidity (operation) | 10 % ... 80 %  |

# THERMOMARK CARD SET PT PT - Thermal transfer printer set



5147219

<https://www.phoenixcontact.com/us/products/5147219>

## Environmental product compliance

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-10   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)