

LPS-10 - Service connector



3270581

<https://www.phoenixcontact.com/us/products/3270581>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Service connector, nom. voltage: 800 V, nominal current: 24 A, number of positions: 1, connection method: Push-in connection, Rated cross section: 2.5 mm², cross section: 0.14 mm²-4 mm², color: red

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3270581 |
| Packing unit | 20 pc |
| Minimum order quantity | 20 pc |
| Sales key | BE29 |
| Product key | BE2Z3X |
| GTIN | 4055626229164 |
| Weight per piece (including packing) | 6.04 g |
| Weight per piece (excluding packing) | 6.04 g |
| Customs tariff number | 85366990 |
| Country of origin | PL |

LPS-10 - Service connector



3270581

<https://www.phoenixcontact.com/us/products/3270581>

Technical data

Product properties

| | |
|---------------------|--------------------------|
| Product type | Test plug terminal block |
| Number of positions | 1 |

Connection data

| | |
|---|--|
| Connection method | Push-in connection |
| Stripping length | 10 mm |
| | 8 mm ... 10 mm |
| Conductor cross-section rigid | 0.14 mm ² ... 4 mm ² |
| Cross section AWG | 26 ... 12 (converted acc. to IEC) |
| Conductor cross-section flexible | 0.14 mm ² ... 4 mm ² |
| Conductor cross-section, flexible [AWG] | 26 ... 12 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.14 mm ² ... 2.5 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.14 mm ² ... 2.5 mm ² |
| Nominal cross section | 2.5 mm ² |
| Nominal current | 24 A |
| Nominal voltage | 800 V |

Connection cross sections directly pluggable

| | |
|---|---|
| Conductor cross-section rigid | 0.5 mm ² ... 2.5 mm ² |
| Conductor cross-section, rigid [AWG] | 20 ... 14 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.5 mm ² ... 2.5 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.5 mm ² ... 2.5 mm ² |

Dimensions

| | |
|--------|---------|
| Width | 10.3 mm |
| Height | 18.3 mm |
| Depth | 63.8 mm |

Material specifications

| | |
|--|----------------|
| Color | red (RAL 3001) |
| Material | PA |
| Flammability rating according to UL 94 | V0 |
| Static insulating material application in cold | -60 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 125 °C |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -60 °C (max. operating temperature see derating curve) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |

LPS-10 - Service connector

3270581

<https://www.phoenixcontact.com/us/products/3270581>



| | |
|--|-----------------|
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

LPS-10 - Service connector



3270581

<https://www.phoenixcontact.com/us/products/3270581>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3270581>

DNV

Approval ID: TAE00004TX

LPS-10 - Service connector



3270581

<https://www.phoenixcontact.com/us/products/3270581>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250304 |
| ECLASS-15.0 | 27250304 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002555 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 20122000 |
|-------------|----------|

LPS-10 - Service connector



3270581

<https://www.phoenixcontact.com/us/products/3270581>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com