

FLKM HDSUB-15/F - Termination board



5528367

<https://www.phoenixcontact.com/us/products/5528367>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with screw connection and High Density D-Subminiature female connector, for mounting on NS 32 or NS 35/7.5, no. of pos.: 15, width: 57 mm

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 5528367 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | NULL |
| Product key | DK2BZZ |
| GTIN | 4017918957834 |
| Weight per piece (including packing) | 147.5 g |
| Weight per piece (excluding packing) | 96.5 g |
| Customs tariff number | 85369010 |
| Country of origin | US |

FLKM HDSUB-15/F - Termination board



5528367

<https://www.phoenixcontact.com/us/products/5528367>

Technical data

Product properties

| | |
|---------------------|------------------|
| Product type | Interface module |
| Number of positions | 15 |

Electrical properties

| | |
|---|-------|
| Nominal voltage U_N | 125 V |
| Max. current carrying capacity per branch | 1 A |

Connection data

Field level

| | |
|----------------------------------|---|
| Connection in acc. with standard | IEC / EN |
| Connection method | Screw connection |
| Stripping length | 8 mm |
| Screw thread | M3 |
| Number of positions | 15 |
| Conductor cross-section rigid | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |

Controller level

| | |
|---------------------|-----------|
| Connection method | pluggable |
| Number of positions | 44 |

Dimensions

Item dimensions

| | |
|--------|-------|
| Width | 57 mm |
| Height | 77 mm |
| Depth | 58 mm |

Material specifications

| | |
|-----------------------------|-----------------------------|
| Color | green (RAL 6021) |
| Housing insulation material | Polyamide PA non-reinforced |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

Mounting

| | |
|-------------------|-----|
| Mounting position | any |
|-------------------|-----|

FLKM HDSUB-15/F - Termination board



5528367

<https://www.phoenixcontact.com/us/products/5528367>

Notes

Notes on operation

For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

FLKM HDSUB-15/F - Termination board




5528367


<https://www.phoenixcontact.com/us/products/5528367>

Drawings

Schematic diagram



Circuit diagram



Universal circuit diagram

FLKM HDSUB-15/F - Termination board



5528367

<https://www.phoenixcontact.com/us/products/5528367>

Environmental product compliance

EU REACH SVHC

| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com