

# UM-DELTA V/A/T/SI/BFI - Passive module



5603254

<https://www.phoenixcontact.com/us/products/5603254>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE interface module with knife disconnection, fuse and fuse failure display



## Commercial data

Item number	5603254
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK218K
GTIN	4017918923075
Weight per piece (including packing)	250 g
Weight per piece (excluding packing)	250 g
Customs tariff number	85369010
Country of origin	US

5603254

<https://www.phoenixcontact.com/us/products/5603254>

## Technical data

### Product properties

Product type	Interface module
Product family	VARIOFACE
Number of positions	16

### Electrical properties

Operating voltage (DC)	24 V DC
Current (per branch)	≤ 50 mA (in as-supplied state, with one 50 mAF fuse, max. 1 A permitted)

Supported controller: EMERSON DeltaV

Suitable I/O card	VE4003S2B4
	VE4005S2B3
	VE4003S2B5

### Connection data

#### Field level

Connection method	Screw connection
Stripping length	7 mm
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

#### Controller level

Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	16
Pitch	2.54 mm

### Signaling

Status display present	yes, if the fuse fails
------------------------	------------------------

### Dimensions

#### Item dimensions

Width	61 mm
Height	126 mm
Depth	71 mm

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

5603254

<https://www.phoenixcontact.com/us/products/5603254>

## Standards and regulations

Standards/regulations	IEC 60664
	IEC 60664A
	DIN VDE 0110
	DIN VDE 0160 (in parts)

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

# UM-DELTA V/A/T/SI/BFI - Passive module





5603254

<https://www.phoenixcontact.com/us/products/5603254>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/5603254>

 <b>cUL Recognized</b> Approval ID: E238705				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	24 V	2 A	-	-

 <b>UL Recognized</b> Approval ID: E238705				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
keine				
	24 V	2 A	-	-

# UM-DELTAV/A/T/SI/BFI - Passive module



5603254

<https://www.phoenixcontact.com/us/products/5603254>

## Classifications

### ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

### ETIM

ETIM 10.0	EC002780
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

5603254

<https://www.phoenixcontact.com/us/products/5603254>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	51f51b91-d909-480b-96dc-a00f481b8fe1

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)