

UM-DELTA V/D/SI - Passive module



5603255

<https://www.phoenixcontact.com/us/products/5603255>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Fuse module with shield connection terminals (for digital cards of the Delta V control system)



Your advantages

- These system-specific interface modules for DeltaV modules are used in combination with the relevant system cables

Commercial data

Item number	5603255
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	DK218K
GTIN	4017918955007
Weight per piece (including packing)	221.1 g
Weight per piece (excluding packing)	221.1 g
Customs tariff number	85369010
Country of origin	US

UM-DELTA V/D/SI - Passive module



5603255

<https://www.phoenixcontact.com/us/products/5603255>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE
Number of positions	16
No. of channels	8

Electrical properties

Nominal voltage U_N	24 V DC
Max. current carrying capacity per branch	50 mA (in as-supplied state, with one 50 mA fuse, max. 1 A permitted)

Supported controller: EMERSON DeltaV

Suitable I/O card	VE4001S2T2B3
	VE4001S2T2B3 Series 2
	VE4001S2T1B3
	VE4002S1T1B3
	VE4002S1T2B3
	VE4002S1T2B3 Series 2

Connection data

Field level

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Controller level

Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	16
Pitch	2.54 mm

Signaling

Status display present	no
------------------------	----

Dimensions

Item dimensions

Width	61 mm
Height	126 mm
Depth	71 mm

UM-DELTA V/D/SI - Passive module



5603255

<https://www.phoenixcontact.com/us/products/5603255>

Material specifications

Housing insulation material	Polyamide PA non-reinforced
-----------------------------	-----------------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--


UM-DELTA V/D/SI - Passive module



5603255

<https://www.phoenixcontact.com/us/products/5603255>

Drawings



Connection scheme UM-DELTA V/D/SI

UM-DELTA V/D/SI - Passive module



5603255

<https://www.phoenixcontact.com/us/products/5603255>

Classifications

UNSPSC

UNSPSC 21.0	39121432
-------------	----------

UM-DELTA V/D/SI - Passive module



5603255

<https://www.phoenixcontact.com/us/products/5603255>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com