

BMK 38X11 YE - Fabric label sheet




5031676

<https://www.phoenixcontact.com/us/products/5031676>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Fabric label sheet, Sheet, yellow (RAL 1018), unmarked, can be labeled with: CMS-P1-PLOTTER, PLOTMARK, mounting type: adhesive, Number of individual labels: 88, text field height: 11 mm, text field width: 38 mm



Your advantages

- Available in various dimensions
- Self-adhesive labels for labeling by hand or with a plotter
- Secure adhesion even on curved or uneven surfaces as well as round corners
- The material file can be downloaded under the Phoenix Contact marking software under Downloads - "Software update - Marking".
- Labeling service: Phoenix Contact can custom-label all BMK ... markers according to your requirements

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 5031676 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BG13 |
| Product key | BG2414 |
| GTIN | 4017918095505 |
| Weight per piece (including packing) | 11.5 g |
| Weight per piece (excluding packing) | 10.25 g |
| Customs tariff number | 39199080 |
| Country of origin | BE |

BMK 38X11 YE - Fabric label sheet



5031676

<https://www.phoenixcontact.com/us/products/5031676>

Technical data

Product properties

| | |
|--------------|---------------|
| Product type | Device marker |
|--------------|---------------|

Marking

| | |
|-------------------------------------|---------|
| Number of individual labels | 88 |
| Number of individual labels per row | 4 |
| Identification technology | Plotter |

Dimensions

| | |
|--------|----------|
| Width | 38.00 mm |
| Height | 11.00 mm |
| Depth | 0.09 mm |

Text field

| | |
|-------------------|-------|
| Text field width | 38 mm |
| Text field height | 11 mm |

Material specifications

| | |
|-----------------------|-------------------|
| Foil strength | 66 µm |
| Adhesive strength | 27.9 µm |
| Adhesive | Acrylic |
| Color | yellow (RAL 1018) |
| Base element material | Polyester |
| Components | Silicone-free |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 80 °C |
| Recommended ambient temperature (storage/transport) | 26 °C |
| Recommended humidity (storage/transport) | 60 % (Storage in a dry and dark place in the original packaging is recommended) |

Test for substances that would hinder coating with paint or varnish

| | |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result | Test passed |

Test for substances that would hinder coating with paint or varnish

| | |
|---|--------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364:2018-05 |
| Result | Test passed |

Scratch resistance

| | |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
|---------------|--------------------------------|

BMK 38X11 YE - Fabric label sheet



5031676

<https://www.phoenixcontact.com/us/products/5031676>

| | |
|--------------|-------------|
| Requirements | ≥ 5 N |
| Result | Test passed |

Tesafilm test

| | |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result | Test passed |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |
| Procedure | Artificial irradiation. |

Temperature resistance

| | |
|------------------------|---------------------------------|
| Specification | ANSI/UL 969-2018:03 (following) |
| Test duration | 240 h |
| Rating 125 °C (150 °C) | Test passed |

Wipe resistance of inscriptions

| | |
|---|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |
| Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2] | Test passed |
| Ethanol (99 %) [CAS No. 64-17-5] | Test passed |

Immersion in chemicals, oil & fuel

| | |
|---|--------------------------|
| Specification | ISO 175:2010 (following) |
| Test duration | 168 h |
| Saltwater (saturated 350 g/l) [CAS No. -] | Test passed |
| Diesel [CAS No. 68476-34-6] | Test passed |
| IRM 901 | Test passed |
| IRM 902 | Test passed |
| IRM 903 | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|----------------------|
| Specification | EN ISO 22479:2022-06 |
| Result | Test passed |
| Procedure | Method B |
| Cycles | 2 |

Salt spray test

BMK 38X11 YE - Fabric label sheet



5031676

<https://www.phoenixcontact.com/us/products/5031676>

| | |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result | Test passed |
| Test duration | 96 h |

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

BMK 38X11 YE - Fabric label sheet



5031676

<https://www.phoenixcontact.com/us/products/5031676>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

BMK 38X11 YE - Fabric label sheet



5031676

<https://www.phoenixcontact.com/us/products/5031676>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com