


SSMK 60X18 - Control cabinet marker

5032439

<https://www.phoenixcontact.com/us/products/5032439>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Control cabinet marker, size: 60 x 18 mm, lettering field: 56 x 14 mm, 2 mounting holes M3, including 1 x ES-SSMK-GB 60 x 18

Your advantages

- The ES-SSMK ... insert strips can be labeled using the CMS-P1-PLOTTER and the CMS-P1-PAD magazine
- The labeling is resistant to external influences
- The base carrier has two fixing holes so that it can be screwed on
- Control cabinet markers consisting of a transparent cap and base carrier
- Once labeled, the insert label is inserted in the cap and this is then snapped onto the base carrier

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 5032439 |
| Packing unit | 50 pc |
| Minimum order quantity | 1 pc |
| Sales key | BG18 |
| Product key | BG241B |
| GTIN | 4017918095802 |
| Weight per piece (including packing) | 4.636 g |
| Weight per piece (excluding packing) | 4.636 g |
| Customs tariff number | 39269097 |
| Country of origin | PL |

SSMK 60X18 - Control cabinet marker



5032439

<https://www.phoenixcontact.com/us/products/5032439>

Technical data

Product properties

| | |
|--------------|-----------------|
| Product type | Marker carriers |
|--------------|-----------------|

Dimensions

| | |
|--------|----------|
| Width | 60.22 mm |
| Height | 18.00 mm |
| Depth | 4.50 mm |

Text field

| | |
|-------------------|-------|
| Text field width | 56 mm |
| Text field height | 14 mm |

Material specifications

| | |
|--|--------------------------------|
| Color | multicolored (RAL -) |
| | white (RAL 9010) |
| | transparent |
| Flammability rating according to UL 94 | V2 |
| Base element material | PC |
| Components | free from silicone and halogen |

Mechanical properties

Technical data

| | |
|--------------------|----------|
| Drill hole spacing | 40.00 mm |
|--------------------|----------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 115 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
|---------------|---------------------------------------|

Wipe resistance of inscriptions

| | |
|---------------|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

Mounting

| | |
|---------------|--------------|
| Mounting type | screw, rivet |
|---------------|--------------|

SSMK 60X18 - Control cabinet marker



5032439

<https://www.phoenixcontact.com/us/products/5032439>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

SSMK 60X18 - Control cabinet marker



5032439

<https://www.phoenixcontact.com/us/products/5032439>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com