

THERMOMARK CARD KIT-GH - Card printer starter set



5146770

<https://www.phoenixcontact.com/us/products/5146770>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Printing set, consisting of THERMOMARK CARD card printer, CLIP-PROJECT PROFESSIONAL software, 50 m ink ribbon, magazines and material: 1440 x terminal labeling, 400 x cable labeling, 20 x rating plate, 1280 x device marking and 10 m marker carrier

Commercial data

Item number	5146770
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BG1221
GTIN	4046356724548
Weight per piece (including packing)	12.23 kg
Weight per piece (excluding packing)	12.23 kg
Country of origin	DE

THERMOMARK CARD KIT-GH - Card printer starter set



5146770

<https://www.phoenixcontact.com/us/products/5146770>

Set consists of

THERMOMARK CARD - Thermal transfer printer

5146464

<https://www.phoenixcontact.com/us/products/5146464>

Thermal transfer printer for cards



CLIP-PROJECT PROFESSIONAL - Software

5146053

<https://www.phoenixcontact.com/us/products/5146053>



Multilingual software for terminal strip configuration. A marking module enables the professional marking of markers and labels for identifying terminal blocks, conductors and cables, and devices.

THERMOMARK CARD KIT-GH - Card printer starter set



5146770

<https://www.phoenixcontact.com/us/products/5146770>

THERMOMARK CARD-UCT-MAG2 - Magazine

5146563

<https://www.phoenixcontact.com/us/products/5146563>

Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets (UCT-TMF...)



EML (26,5X12)R SR - Label

0816854

<https://www.phoenixcontact.com/us/products/0816854>



Label, Roll, unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, Number of individual labels: 2500, text field height: 12 mm, text field width: 26.5 mm

THERMOMARK CARD KIT-GH - Card printer starter set



5146770

<https://www.phoenixcontact.com/us/products/5146770>

UCT-TMF 5 - Marker for terminal blocks

0828744

<https://www.phoenixcontact.com/us/products/0828744>



Marker for terminal blocks, Sheet, white (RAL 9010), unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME 2.0, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, TOPMARK NEO, TOPMARK LASER, mounting type: latching, for terminal block width: 5.2 mm, Number of individual labels: 72, text field height: 4.7 mm, text field width: 4.4 mm

US-EMP (17X15) - Snap-in markers

0828774

<https://www.phoenixcontact.com/us/products/0828774>



Snap-in markers, Card, white (RAL 9010), unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0, mounting type: latching, Number of individual labels: 54, text field height: 15 mm, text field width: 17 mm

THERMOMARK CARD KIT-GH - Card printer starter set



5146770

<https://www.phoenixcontact.com/us/products/5146770>

US-EML (17,5X8) - Label

0800461

<https://www.phoenixcontact.com/us/products/0800461>



Label, Card, white (RAL 9010), unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0, mounting type: adhesive, Number of individual labels: 80, text field height: 8 mm, text field width: 17.5 mm

US-WML 6 (13X13) - Cable marker label

0800472

<https://www.phoenixcontact.com/us/products/0800472>



Cable marker label, Card, white (RAL 9010), unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0, cable diameter range: 4 ... 6 mm, mounting type: adhesive, cable diameter: ≤ 6 mm, Number of individual labels: 32, text field height: 13 mm, text field width: 13 mm

THERMOMARK CARD KIT-GH - Card printer starter set



5146770

<https://www.phoenixcontact.com/us/products/5146770>

US-WML 14 (25X19) - Cable marker label

0800473

<https://www.phoenixcontact.com/us/products/0800473>



Cable marker label, Card, white (RAL 9010), unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0, cable diameter range: 6.1 ... 14 mm, mounting type: adhesive, cable diameter: ≤ 14 mm, Number of individual labels: 8, text field height: 19 mm, text field width: 25 mm

CARRIER/L-EMP (1000X15) GY - Marker carriers

0829559

<https://www.phoenixcontact.com/us/products/0829559>



Profile, self-adhesive, 1000 mm long, for accommodating UC-,/US-, LS-, and EMT (EX15)R material, 15 mm height

THERMOMARK CARD KIT-GH - Card printer starter set



5146770

<https://www.phoenixcontact.com/us/products/5146770>

Technical data

Product properties

Product type	Marking system
--------------	----------------

Marking

Identification technology	Thermotransfer
---------------------------	----------------

Device properties

Print width	104 mm
Operating system	MS Windows 7, MS Windows 8.1, MS Windows 10

Electrical properties

Supply

Supply voltage range	100 V AC ... 240 V AC (50 Hz ... 60 Hz)
----------------------	---

Dimensions

Width	253 mm
Height	189 mm
Length	320 mm

Material specifications

Color	gray
-------	------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	5 °C ... 35 °C
Permissible humidity (operation)	10 % ... 80 %

THERMOMARK CARD KIT-GH - Card printer starter set



5146770

<https://www.phoenixcontact.com/us/products/5146770>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com