

UMK 22 REL 24AC/21-ST - Active module



5521115

<https://www.phoenixcontact.com/us/products/5521115>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE relay module, pluggable, 1PDT



UMK 22 REL 24 VAC/21-21 shown

Commercial data

Item number	5521115
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C460
Product key	DK6165
GTIN	4046356688314
Weight per piece (including packing)	33.33 g
Weight per piece (excluding packing)	33.33 g
Customs tariff number	85364190
Country of origin	US

UMK 22 REL 24AC/21-ST - Active module



5521115

<https://www.phoenixcontact.com/us/products/5521115>

Technical data

Product properties

Product type	Multi-channel relay module
No. of channels	1

Input data

Nominal input voltage U_N	24 V AC
Input voltage range in reference to U_N	0.8 ... 1.1
Input voltage range	19.2 V AC ... 26.4 V AC
Typical input current at U_N	2 mA (LED display)
Operating voltage display	Yellow LED
Status display/channel	Yellow LED

Output data

Switching

Contact switching type	1 changeover contact
Maximum switching voltage	250 V AC (30 V DC)
Limiting continuous current	10 A
Error detection (line break / short-circuit)	no

Connection data

Input

Connection method	Screw connection
Screw thread	M3
Number of connections	2
Number of positions	2
Conductor cross-section rigid	0.14 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross-section AWG	28 ... 14

Dimensions

Width	22.5 mm
Height	77 mm
Depth	50 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	PA

Environmental and real-life conditions

Ambient conditions

UMK 22 REL 24AC/21-ST - Active module



5521115

<https://www.phoenixcontact.com/us/products/5521115>

Ambient temperature (operation)	-20 °C ... 65 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Mounting

Mounting position	any
-------------------	-----

5521115

<https://www.phoenixcontact.com/us/products/5521115>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com