

UMK 22-REL 24/21-ST (BASE) - Relay base




5529188

<https://www.phoenixcontact.com/us/products/5529188>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE base module for G2R relay, 1PDT



Your advantages

- Relay base family that can be fitted with 1 changeover contact relay
- Safe isolation between coil and contact side
- For use with Omron G2R-1-S relays
- DIN rail mounting

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 5529188 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C460 |
| Product key | DK61Y2 |
| GTIN | 4046356684156 |
| Weight per piece (including packing) | 33.33 g |
| Weight per piece (excluding packing) | 33.33 g |
| Customs tariff number | 85364190 |
| Country of origin | US |

5529188

<https://www.phoenixcontact.com/us/products/5529188>

Technical data

Product properties

| | |
|----------------|-----------------------|
| Product type | Relay socket |
| Application | Universal |
| Operating mode | 100% operating factor |

Electrical properties

| | |
|-----------------------|-------------|
| Nominal voltage U_N | 250 V AC/DC |
| Nominal current I_N | 10 A |

Connection data

Input side

| | |
|----------------------------------|--|
| Connection method | Screw connection |
| Stripping length | 6 mm |
| Screw thread | M3 |
| Conductor cross-section rigid | 0.14 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.14 mm ² ... 1.5 mm ² |
| Conductor cross-section AWG | 30 ... 14 |

Output side

| | |
|----------------------------------|--|
| Connection method | Screw connection |
| Stripping length | 6 mm |
| Screw thread | M3 |
| Conductor cross-section rigid | 0.14 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.14 mm ² ... 1.5 mm ² |
| Conductor cross-section AWG | 30 ... 14 |

Dimensions

| | |
|-------------------------|--------------------------------|
| Width | 22.5 mm |
| Height | 77 mm |
| Depth Retaining bracket | 50 mm (with retaining bracket) |

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 65 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

Mounting

| | |
|-------------------|---------------------------|
| Mounting type | DIN rail mounting |
| Assembly note | in rows with zero spacing |
| Mounting position | any |

UMK 22-REL 24/21-ST (BASE) - Relay base



5529188

<https://www.phoenixcontact.com/us/products/5529188>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27371603 |
| ECLASS-15.0 | 27371603 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001456 |
|----------|----------|

UMK 22-REL 24/21-ST (BASE) - Relay base



5529188

<https://www.phoenixcontact.com/us/products/5529188>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
|-------------------------------------|----------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com