

EM-DUO 120/20/SWA - Socket



5604435

<https://www.phoenixcontact.com/us/products/5604435>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Socket, connection method: Screw connection, color: ivory, nom. voltage: 125 V AC, nominal current: 20 A, standards/specifications: UL 508, CSA 22.2

Commercial data

Item number	5604435
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE76
Product key	BE7613
GTIN	4046356684484
Weight per piece (including packing)	33.33 g
Weight per piece (excluding packing)	33.33 g
Customs tariff number	85366990
Country of origin	US

Technical data

Notes

Trade restriction

CE note	The products are offered exclusively for export outside the EU and the European Economic Area.
---------	--

Product properties

Product type	Socket
For country-specific use in	USA
	Canada
	Japan
	Mexico
	Saudi Arabia
	Taiwan
	Venezuela

Connection data

Connection method	Screw connection
Screw thread	M3
Stripping length	8 mm
Conductor cross-section rigid	0.2 mm ² ... 6 mm ²
Cross section AWG	30 ... 10 (converted acc. to IEC)
Conductor cross-section flexible	0.2 mm ² ... 4 mm ²
Nominal current	20 A
Nominal voltage	125 V AC

Material specifications

Color	ivory (RAL 1014)
Flammability rating according to UL 94	V0
Insulating material	PVC 94 V0
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Environmental and real-life conditions

EM-DUO 120/20/SWA - Socket



5604435

<https://www.phoenixcontact.com/us/products/5604435>

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-35 °C ... 70 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Standards

Standards/regulations	UL 508
	CSA 22.2

EM-DUO 120/20/SWA - Socket





5604435

<https://www.phoenixcontact.com/us/products/5604435>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/5604435>

 UL Listed Approval ID: E238705				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	120 V	20 A	30 - 10	30 - 10

 cUL Listed Approval ID: E238705				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	120 V	20 A	30 - 10	-

EM-DUO 120/20/SWA - Socket



5604435

<https://www.phoenixcontact.com/us/products/5604435>

Classifications

ECLASS

ECLASS-13.0	27142305
ECLASS-15.0	27142305

ETIM

ETIM 10.0	EC001663
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

EM-DUO 120/20/SWA - Socket



5604435

<https://www.phoenixcontact.com/us/products/5604435>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, Not qualified for the European market
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com