

# RAD-CAB-PFP600-25 - Coaxial cable



5606126

<https://www.phoenixcontact.com/us/products/5606126>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Antenna cable, outside diameter: 15 mm (0.6 in.), inner conductor: solid, attenuation: 1.0 / 1.3 / 2.0 dB at 0.9 / 2.4 / 5.8 GHz, connection: 2x N (male), cable length: 7.5 m (25 ft.)



## Your advantages

- Low attenuation
- UV resistant
- For outdoor installation

## Commercial data

Item number	5606126
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DN23
Product key	DNC6A3
GTIN	4046356683937
Weight per piece (including packing)	2,200 g
Weight per piece (excluding packing)	1,677 g
Customs tariff number	85442000
Country of origin	CN

# RAD-CAB-PFP600-25 - Coaxial cable



5606126

<https://www.phoenixcontact.com/us/products/5606126>

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Coaxial cable
--------------	---------------

### Electrical properties

Frequency range	400 MHz ... 5.8 GHz
Impedance	50 $\Omega$

### Connection data

#### Connector connection

Connection method	N(m)
Notes	Both sides

### Cable/line

Cable length	7.5 m
Cable type	PFP-600
External sheath, color	black
868 / 900 MHz	1 dB
2.4 GHz	1.3 dB

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

# RAD-CAB-PFP600-25 - Coaxial cable



5606126

<https://www.phoenixcontact.com/us/products/5606126>

## Classifications

### ECLASS

ECLASS-15.0	27060310
ECLASS-13.0	27060310

### ETIM

ETIM 10.0	EC001682
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# RAD-CAB-PFP600-25 - Coaxial cable



5606126

<https://www.phoenixcontact.com/us/products/5606126>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	cbaa8f2e-cbef-4c71-bffe-dfca3f8241b9

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)