

WMTB HF (40X12)R RD CUS - Cable marker



8191197

<https://www.phoenixcontact.com/us/products/8191197>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker, Roll, can be ordered: by line, red (RAL 3001), labeled according to customer specifications, mounting type: Assembly with cable ties, cable diameter: ≥ 6 mm, Number of individual labels: 1000, text field height: 12 mm, text field width: 40 mm

Your advantages

- The WMTB HF ... conductor and cable marking is used for the identification and bundling conductors and cables indoors and outdoors
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- The markers are made of a halogen-free material
- The highly flexible material adapts to the conductors and cables
- The marker has two fastening eyes so that it can be attached to the conductor by means of WT cable binders

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 8191197 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | BG8131 |
| GTIN | 4055626024318 |
| Weight per piece (including packing) | 1.7 g |
| Weight per piece (excluding packing) | 99.99 g |
| Country of origin | PL |

WMTB HF (40X12)R RD CUS - Cable marker



8191197

<https://www.phoenixcontact.com/us/products/8191197>

Technical data

Product properties

| | |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

Marking

| | |
|-------------------------------------|----------------|
| Number of individual labels | 1000 |
| Number of individual labels per row | 1 |
| Identification technology | Thermotransfer |

Dimensions

| | |
|--------|-------|
| Width | 10 mm |
| Length | 40 mm |

Text field

| | |
|-------------------|-------|
| Text field width | 40 mm |
| Text field height | 12 mm |

Material specifications

| | |
|--|-------------------------|
| RoHS compliant | yes |
| Color | red (RAL 3001) |
| Material | PUR |
| Flammability rating according to UL 94 | V2 (0,75 mm Wandstärke) |
| Base element material | PUR |
| Components | halogen-free |

Cable/line

| | |
|-------------------------|-----------|
| External cable diameter | ≥ 6.00 mm |
|-------------------------|-----------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|-------------------|
| Ambient temperature (operation) | -25 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 10 °C |
| Recommended humidity (storage/transport) | 45 % ... 55 % |

Test for substances that would hinder coating with paint or varnish

| | |
|---|--------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364:2018-05 |
| Result | Test passed |

Scratch resistance

| | |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements | ≥ 5 N |
| Result | Test passed |

Tesafilm test

WMTB HF (40X12)R RD CUS - Cable marker



8191197

<https://www.phoenixcontact.com/us/products/8191197>

| | |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result | Test passed |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |
| Procedure | Artificial irradiation. |

Temperature resistance

| | |
|------------------------|---------------------------------|
| Specification | ANSI/UL 969-2018:03 (following) |
| Test duration | 240 h |
| Rating 125 °C (150 °C) | Test passed |

Wipe resistance of inscriptions

| | |
|---|--|
| Specification | DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |
| Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2] | Test passed |

Immersion in chemicals, oil & fuel

| | |
|---|--------------------------|
| Specification | ISO 175:2010 (following) |
| Test duration | 168 h |
| Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2] | Test passed |
| Saltwater (saturated 350 g/l) [CAS No. -] | Test passed |
| Ethanol (99 %) [CAS No. 64-17-5] | Test passed |
| Diesel [CAS No. 68476-34-6] | Test passed |
| IRM 901 | Test passed |
| IRM 902 | Test passed |
| IRM 903 | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|--------------------------|
| Specification | DIN EN ISO 22479:2022-08 |
| Result | Test passed |
| Procedure | Method B |
| Cycles | 2 |

Salt spray test

| | |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result | Test passed |

WMTB HF (40X12)R RD CUS - Cable marker



8191197

<https://www.phoenixcontact.com/us/products/8191197>

| | |
|---------------|------|
| Test duration | 96 h |
|---------------|------|

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|--------------------------|
| Mounting type | Assembly with cable ties |
|---------------|--------------------------|

WMTB HF (40X12)R RD CUS - Cable marker



8191197

<https://www.phoenixcontact.com/us/products/8191197>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281102 |
| ECLASS-15.0 | 27281102 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001530 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

WMTB HF (40X12)R RD CUS - Cable marker



8191197

<https://www.phoenixcontact.com/us/products/8191197>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com