

EML-RS (45,7X45,7)R SR CUS - Label



8191372

<https://www.phoenixcontact.com/us/products/8191372>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, Roll, labeled according to customer specifications, mounting type: adhered, inserted, Number of individual labels: 1, text field height: 45.7 mm, text field width: 45.7 mm

Your advantages

- The EML-RS label for marking rotary switches from Phoenix Contact
- Options include adhesive and snap-in versions
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- The EML-RS... materials are UL-listed
- Labeling service: Phoenix Contact can custom-label all EML-RS ... markers in accordance with your requirements

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 8191372 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Product key | BG8141 |
| GTIN | 4055626048529 |
| Weight per piece (including packing) | 2.1 g |
| Weight per piece (excluding packing) | 2.1 g |
| Country of origin | PL |

Technical data

Product properties

| | |
|---------------------|-----------------------|
| Product type | Device marker |
| Area of application | Rotary switch Ø 25 mm |

Marking

| | |
|-------------------------------------|----------------|
| Number of individual labels | 1 |
| Number of individual labels per row | 1 |
| Identification technology | Thermotransfer |

Dimensions

| | |
|--------|----------|
| Width | 45.40 mm |
| Height | 45.40 mm |
| Depth | 0.10 mm |

Text field

| | |
|-------------------|---------|
| Text field width | 45.7 mm |
| Text field height | 45.7 mm |

Material specifications

| | |
|-----------------------|--------------------------------|
| Color | silver-colored |
| Base element material | Polyester |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 150 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

Test for substances that would hinder coating with paint or varnish

| | |
|---|--------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VDMA 24364:2018-05 |
| Result | Test passed |

Scratch resistance

| | |
|---------------|--------------------------------|
| Specification | EN ISO 1518-1:2023 (following) |
| Requirements | ≥ 5 N |
| Result | Test passed |

Tesafilm test

| | |
|---------------|-------------------------------------|
| Specification | DIN EN ISO 2409:2020-12 (following) |
| Result | Test passed |

EML-RS (45,7X45,7)R SR CUS - Label



8191372

<https://www.phoenixcontact.com/us/products/8191372>

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |
| Procedure | Artificial irradiation. |

Temperature resistance

| | |
|------------------------|---------------------------------|
| Specification | ANSI/UL 969-2018:03 (following) |
| Test duration | 240 h |
| Rating 125 °C (150 °C) | Test passed |

Wipe resistance of inscriptions

| | |
|---|---|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |
| Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2] | Test passed |
| Ethanol (99 %) [CAS No. 64-17-5] | Test passed |

Immersion in chemicals, oil & fuel

| | |
|---|--------------------------|
| Specification | ISO 175:2010 (following) |
| Test duration | 168 h |
| Saltwater (saturated 350 g/l) [CAS No. -] | Test passed |
| Ethanol (99 %) [CAS No. 64-17-5] | Test passed |
| IRM 901 | Test passed |
| IRM 902 | Test passed |
| IRM 903 | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|--------------------------|
| Specification | DIN EN ISO 22479:2022-08 |
| Result | Test passed |
| Procedure | Method B |
| Cycles | 2 |

Salt spray test

| | |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result | Test passed |
| Test duration | 96 h |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

EML-RS (45,7X45,7)R SR CUS - Label



8191372

<https://www.phoenixcontact.com/us/products/8191372>

Mounting

| | |
|---------------|-------------------|
| Mounting type | adhered, inserted |
|---------------|-------------------|

EML-RS (45,7X45,7)R SR CUS - Label



8191372

<https://www.phoenixcontact.com/us/products/8191372>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

EML-RS (45,7X45,7)R SR CUS - Label



8191372

<https://www.phoenixcontact.com/us/products/8191372>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com