

# EML-RS (45,7X45,7)R SR CUS - Label



8191372

<https://www.phoenixcontact.com/us/products/8191372>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, Roll, labeled according to customer specifications, mounting type: adhered, inserted, Number of individual labels: 1, text field height: 45.7 mm, text field width: 45.7 mm

## Your advantages

- The EML-RS label for marking rotary switches from Phoenix Contact
- Options include adhesive and snap-in versions
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- The EML-RS... materials are UL-listed
- Labeling service: Phoenix Contact can custom-label all EML-RS ... markers in accordance with your requirements

## Commercial data

Item number	8191372
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8141
GTIN	4055626048529
Weight per piece (including packing)	2.1 g
Weight per piece (excluding packing)	2.1 g
Country of origin	PL

## Technical data

### Product properties

Product type	Device marker
Area of application	Rotary switch Ø 25 mm

### Marking

Number of individual labels	1
Number of individual labels per row	1
Identification technology	Thermotransfer

### Dimensions

Width	45.40 mm
Height	45.40 mm
Depth	0.10 mm

### Text field

Text field width	45.7 mm
Text field height	45.7 mm

### Material specifications

Color	silver-colored
Base element material	Polyester
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364:2018-05
Result	Test passed

#### Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

#### Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

# EML-RS (45,7X45,7)R SR CUS - Label



8191372

<https://www.phoenixcontact.com/us/products/8191372>

## UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

## Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 125 °C (150 °C)	Test passed

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed

## Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Saltwater (saturated 350 g/l) [CAS No. - ]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

## Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

# EML-RS (45,7X45,7)R SR CUS - Label



8191372

<https://www.phoenixcontact.com/us/products/8191372>

## Mounting

Mounting type	adhered, inserted
---------------	-------------------

# EML-RS (45,7X45,7)R SR CUS - Label



8191372

<https://www.phoenixcontact.com/us/products/8191372>

## Classifications

### ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

### ETIM

ETIM 10.0	EC001288
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# EML-RS (45,7X45,7)R SR CUS - Label



8191372

<https://www.phoenixcontact.com/us/products/8191372>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)