

QUINT4-S-ORING/12-24DC/1X40/+ - Redundancy module, with protective coating



2907753

<https://www.phoenixcontact.com/gb/products/2907753>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Active QUINT single redundancy module for DIN rail mounting, protective coating, input: 12 V DC ... 24 V DC, output: 12 V DC ... 24 V DC / 1 x 40 A, integrated surge protection <28.8 V DC, incl. mounted UTA 107/30 universal DIN rail adapter

Product description

Active redundancy module for superior system availability and maximum operational reliability. QUINT S-ORING enables the separate structuring of a redundant system. In combination with the new QUINT POWER power supply, the redundant system is monitored continuously.

Your advantages

- Consistent redundancy up to the load
- Input voltage and decoupling section monitored on a permanent basis
- Save energy by decoupling with MOSFET
- Protection against surge voltages in excess of 30 V DC at the output

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2907753 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | CMRI43 |
| Product key | CMRI43 |
| GTIN | 4055626231914 |
| Weight per piece (including packing) | 471.5 g |
| Weight per piece (excluding packing) | 413.78 g |
| Customs tariff number | 85371091 |
| Country of origin | CN |

QUINT4-S-ORING/12-24DC/1X40/+ - Redundancy module, with protective coating



2907753

<https://www.phoenixcontact.com/gb/products/2907753>

Technical data

Input data

DC operation

| | |
|---------------------------------------|---------------------------|
| Nominal input voltage range | 12 V DC ... 24 V DC |
| Input voltage range | 8 V DC ... 26 V DC (SELV) |
| Typical national grid voltage | 12 V DC |
| | 24 V DC |
| Voltage type of supply voltage | DC |
| Current consumption | 40 A |
| Static Boost ($I_{Stat.Boost}$) | 45 A |
| Dynamic Boost ($I_{Dyn.Boost}$) | 60 A (5 s) |
| Selective Fuse Breaking (I_{SFB}) | 215 A (15 ms) |
| Reverse polarity protection | yes, < 60 V |
| Nominal input current (I_N) | 40 A (-40 °C ... 60 °C) |
| Input current I_{Static} | 45 A (40 °C) |
| Input current $I_{Dynamic}$ | 60 A (5 s) |
| Input current I_{SFB} | 215 A (15 ms) |
| Transient surge protection | Varistor |
| Voltage drop, input/output | 0.1 V DC |

Output data

| | |
|--|---------------------------|
| Efficiency | typ. 99 % (12 V DC) |
| | typ. 99.2 % (24 V DC) |
| Nominal output voltage | $U_{in} - 0,1$ V DC |
| Nominal output current (I_N) | 40 A |
| Static Boost ($I_{Stat.Boost}$) | 45 A |
| Dynamic Boost ($I_{Dyn.Boost}$) | 60 A (5 s) |
| Selective Fuse Breaking (I_{SFB}) | 215 A (15 ms) |
| Derating | 60 °C ... 70 °C (2.5 %/K) |
| Protection against overvoltage at the output (OVP) | < 28.8 V DC |
| Power loss nominal load max. | 6.5 W ($I_{OUT} = 40$ A) |
| | 6 W ($I_{OUT} = 40$ A) |
| Connection in series | no |

Signal: OK, 13/14

| | |
|---------------------------|--------------------------------|
| Output description | Group contact |
| Maximum switching voltage | max. 30 V AC/DC |
| Maximum inrush current | ≤ 100 mA (short-circuit-proof) |

Signal relay 13/14

| | |
|---------|------|
| Default | open |
|---------|------|

QUINT4-S-ORING/12-24DC/1X40/+ - Redundancy module, with protective coating



2907753

<https://www.phoenixcontact.com/gb/products/2907753>

Signal relay 13/14

| | |
|---------|--------|
| Default | closed |
|---------|--------|

Signal relay 13/14

| | |
|---------|------|
| Default | open |
|---------|------|

Signal relay 13/14

| | |
|---------|------|
| Default | open |
|---------|------|

Connection data

Input

| | |
|--|---------------------|
| Connection method | Screw connection |
| Conductor cross-section, rigid min. | 0.5 mm ² |
| Conductor cross-section, rigid max. | 16 mm ² |
| Conductor cross-section flexible min. | 0.5 mm ² |
| Conductor cross-section flexible max. | 16 mm ² |
| Single conductor/flexible terminal point with ferrule with plastic sleeve, min. | 0.5 mm ² |
| Single conductor/flexible terminal point with ferrule with plastic sleeve, max. | 16 mm ² |
| Single conductor/flexible terminal point with ferrule without plastic sleeve, min. | 0.5 mm ² |
| Single conductor/flexible terminal point with ferrule without plastic sleeve, max. | 16 mm ² |
| Conductor cross-section AWG min. | 20 |
| Conductor cross-section AWG max. | 6 |
| Stripping length | 10 mm |
| Screw thread | M4 |
| Tightening torque, min | 1.2 Nm |
| Tightening torque max | 1.5 Nm |

Output

| | |
|--|---------------------|
| Connection method | Screw connection |
| Conductor cross-section, rigid min. | 0.5 mm ² |
| Conductor cross-section, rigid max. | 16 mm ² |
| Conductor cross-section flexible min. | 0.5 mm ² |
| Conductor cross-section flexible max. | 16 mm ² |
| Single conductor/flexible terminal point with ferrule with plastic sleeve, min. | 0.5 mm ² |
| Single conductor/flexible terminal point with ferrule with plastic sleeve, max. | 16 mm ² |
| Single conductor/flexible terminal point with ferrule without plastic sleeve, min. | 0.5 mm ² |
| Single conductor/flexible terminal point with ferrule without plastic sleeve, max. | 16 mm ² |

QUINT4-S-ORING/12-24DC/1X40/+ - Redundancy module, with protective coating



2907753

<https://www.phoenixcontact.com/gb/products/2907753>

| | |
|----------------------------------|--------|
| Conductor cross-section AWG min. | 20 |
| Conductor cross-section AWG max. | 6 |
| Stripping length | 10 mm |
| Screw thread | M4 |
| Tightening torque, min | 1.2 Nm |
| Tightening torque max | 1.5 Nm |

Signal

| | |
|--|----------------------|
| Connection method | Push-in connection |
| Conductor cross-section, rigid min. | 0.2 mm ² |
| Conductor cross-section, rigid max. | 1.5 mm ² |
| Conductor cross-section flexible min. | 0.2 mm ² |
| Conductor cross-section flexible max. | 1.5 mm ² |
| Single conductor/flexible terminal point with ferrule with plastic sleeve, min. | 0.2 mm ² |
| Single conductor/flexible terminal point with ferrule with plastic sleeve, max. | 0.75 mm ² |
| Single conductor/flexible terminal point with ferrule without plastic sleeve, min. | 0.2 mm ² |
| Single conductor/flexible terminal point with ferrule without plastic sleeve, max. | 1.5 mm ² |
| Conductor cross-section AWG min. | 24 |
| Conductor cross-section AWG max. | 16 |
| Stripping length | 8 mm |

Signaling

| | |
|--------------------|--|
| Types of signaling | Relay contact, floating, current limited |
|--------------------|--|

Signal output: OK, 13/14

| | |
|------------------------------|--|
| $U_{in} < 8 \text{ V DC}$ | LED off, input voltage not present or short circuit at redundancy module output |
| $U_{in} > 8 \text{ V DC}$ | LED lights up green, input voltage present |
| $U_{in} > 28.8 \text{ V DC}$ | LED flashing red, OVP active - input voltage exceeds the permissible voltage value |
| Redundancy modul faulty | LED lights up red, redundancy module needs to be factory tested |

Electrical properties

| | |
|--|----------|
| Insulation voltage input, output / housing | 500 V DC |
|--|----------|

Product properties

| | |
|----------------------------|----------------------|
| Product type | Redundancy module |
| Product family | QUINT S-ORING |
| MTBF (IEC 61709, SN 29500) | > 13486000 h (25 °C) |
| | > 7314000 h (40 °C) |
| | > 3379000 h (60 °C) |
| LED | yes |

QUINT4-S-ORING/12-24DC/1X40/+ - Redundancy module, with protective coating



2907753

<https://www.phoenixcontact.com/gb/products/2907753>

Insulation characteristics

| | |
|---------------------|-----|
| Protection class | III |
| Degree of pollution | 2 |


Life expectancy (electrolytic capacitors)

| | |
|-----------------|----------|
| Current | 40 A |
| Temperature | 40 °C |
| Time | 160000 h |
| Additional text | 12 V DC |

Life expectancy (electrolytic capacitors)

| | |
|-----------------|----------|
| Current | 40 A |
| Temperature | 40 °C |
| Time | 149000 h |
| Additional text | 24 V DC |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 32 mm |
| Height | 130 mm |
| Depth | 125 mm |

Installation dimensions

| | |
|----------------------------------|---------------|
| Installation distance right/left | 0 mm / 0 mm |
| Installation distance top/bottom | 40 mm / 20 mm |

Alternative assembly

| | |
|--------|--------|
| Width | 122 mm |
| Height | 130 mm |
| Depth | 35 mm |

Mounting

| | |
|-------------------|---|
| Mounting type | DIN rail mounting |
| Assembly note | alignable: $P_N \geq 50\%$, 5 mm horizontally, 15 mm next to active components, 50 mm vertically alignable: $P_N < 50\%$, 0 mm horizontally, 40 mm vertically top, 20 mm vertically bottom |
| Mounting position | horizontal DIN rail NS 35, EN 60715 |

QUINT4-S-ORING/12-24DC/1X40/+ - Redundancy module, with protective coating



2907753

<https://www.phoenixcontact.com/gb/products/2907753>

Material specifications

| | |
|--|---|
| Flammability rating according to UL 94 (housing / terminal blocks) | V0 |
| Housing material | Metal |
| Housing material | Aluminum / stainless steel |
| Type of housing | Aluminum (AlMg3) |
| Hood version | Galvanized sheet steel, free from chrome (VI) |

Environmental and real-life conditions

Ambient conditions

| | |
|--|--|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 70 °C (> 60 °C Derating: 2,5 %/K) |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Maximum altitude | ≤ 5000 m (> 2000 m, observe derating) |
| Climatic class | 3K22 (in accordance with EN 60721-3-3) |
| Max. permissible relative humidity (operation) | ≤ 100 % (at 25 °C, non-condensing) |
| Shock | 18 ms, 30g, in each space direction (according to IEC 60068-2-27) |
| Vibration (operation) | < 15 Hz, amplitude ±2.5 mm (according to IEC 60068-2-6) 15 Hz ... 150 Hz, 2.3g, 90 min. |
| Temp code | T4 (-25 ... +70 °C; > 60 °C, Derating: 2,5 %/K) |

Standards and regulations

| | |
|-------------------------------------|-------------|
| Standard - Electrical safety | IEC 62368-1 |
| Standard – Safety extra-low voltage | IEC 62368-1 |

Fire protection in rail vehicles

| | |
|--------------------------|----------------------------------|
| Standard designation | Fire protection in rail vehicles |
| Standards/specifications | EN 45545-2 (HL3) |

Approvals

| | |
|-----------------------|---|
| Shipbuilding approval | DNV, NK |
| UL approvals | UL/C-UL listed UL 508 |
| | UL/C-UL Recognized UL 60950-1 |
| | UL 121201 & CSA C22.2 No. 213-17 Class I, Division 2, Groups A, B, C, D T4 (Hazardous Location) |

Conformity/Approvals

| | |
|--|---|
| ATEX | ⊕ II 3 G Ex ec nC IIC T4 Gc |
| | SIQ 21 ATEX 183 X / PTB 24 ATEX 2001 X |
| IECEX | Ex ec nC IIC T4 Gc |
| | IECEX SIQ 21.0001X / IECEX PTB 24.0003X |
| Functional Safety in accordance with IEC 61508 | SIL3 in accordance with IEC 61508-1 (in combination with product 2904602 QUINT4-PS/1AC/24DC/20) |

QUINT4-S-ORING/12-24DC/1X40/+ - Redundancy module, with protective coating



2907753

<https://www.phoenixcontact.com/gb/products/2907753>

EMC data

| | |
|-------------------------------------|---|
| Electromagnetic compatibility | Conformance with EMC Directive 2014/30/EU |
| Low Voltage Directive | Conformance with Low Voltage Directive 2014/35/EC |
| EMC requirements for noise emission | EN 61000-6-3 |
| | EN 61000-6-4 |
| EMC requirements for noise immunity | EN 61000-6-1 |
| | EN 61000-6-2 |

Conducted noise emission

| | |
|-----------------------|------------------------|
| Standards/regulations | EN 55016 |
| | EN 61000-6-3 (Class B) |

Noise emission

| | |
|-----------------------|--|
| Standards/regulations | Additional basic standard EN 61000-6-5 (immunity in power station) |
|-----------------------|--|

Noise emission

| | |
|-----------------------|------------------------|
| Standards/regulations | EN 55016 |
| | EN 61000-6-3 (Class B) |

DNV GL conducted noise emissions

| | |
|-----------------|-------------------------|
| DNV | Class A |
| Additional text | Area power distribution |

DNV GL noise radiation

| | |
|-----------------|----------------------|
| DNV | Class B |
| Additional text | Bridge and deck area |

Electrostatic discharge

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-2 |
|-----------------------|--------------|

Electrostatic discharge

| | |
|-------------------|----------------------|
| Contact discharge | 8 kV (Test Level 4) |
| Discharge in air | 15 kV (Test Level 4) |
| Comments | Criterion A |

Electromagnetic HF field

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-3 |
|-----------------------|--------------|

Electromagnetic HF field

| | |
|---------------------|-----------------------|
| Frequency range | 80 MHz ... 1 GHz |
| Test field strength | 20 V/m (Test Level 3) |
| Frequency range | 1 GHz ... 6 GHz |
| Test field strength | 10 V/m (Test Level 3) |
| Comments | Criterion A |

Fast transients (burst)

QUINT4-S-ORING/12-24DC/1X40/+ - Redundancy module, with protective coating



2907753

<https://www.phoenixcontact.com/gb/products/2907753>

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-4 |
|-----------------------|--------------|

Fast transients (burst)

| | |
|----------|------------------------------------|
| Input | 2 kV (Test Level 3 - asymmetrical) |
| Output | 2 kV (Test Level 3 - asymmetrical) |
| Signal | 2 kV (Test Level 4 - asymmetrical) |
| Comments | Criterion B |

Surge voltage load (surge)

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-5 |
|-----------------------|--------------|

Surge voltage load (surge)

| | |
|----------|------------------------------------|
| Input | 1 kV (Test Level 3 - symmetrical) |
| | 2 kV (Test Level 3 - asymmetrical) |
| Output | 1 kV (Test Level 3 - symmetrical) |
| | 2 kV (Test Level 3 - asymmetrical) |
| Signal | 1 kV (Test Level 2 - asymmetrical) |
| Comments | Criterion A |

Conducted interference

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-6 |
|-----------------------|--------------|

Conducted interference

| | |
|---------------------|----------------------|
| Input/output/signal | asymmetrical |
| Frequency range | 0.15 MHz ... 100 MHz |
| Comments | Criterion A |
| Voltage | 20 V (Test Level 3) |

Criteria

| | |
|-------------|--|
| Criterion A | Normal operating behavior within the specified limits. |
| Criterion B | Temporary impairment to operational behavior that is corrected by the device itself. |

QUINT4-S-ORING/12-24DC/1X40/+ - Redundancy module, with protective coating




2907753

<https://www.phoenixcontact.com/gb/products/2907753>

Drawings

Dimensional drawing




QUINT4-S-ORING/12-24DC/1X40/+ - Redundancy module, with protective coating


2907753

<https://www.phoenixcontact.com/gb/products/2907753>

Dimensional drawing



Diagram




QUINT4-S-ORING/12-24DC/1X40/+ - Redundancy module, with protective coating


2907753

<https://www.phoenixcontact.com/gb/products/2907753>

Diagram



Block diagram



QUINT4-S-ORING/12-24DC/1X40/+ - Redundancy module, with protective coating



2907753

<https://www.phoenixcontact.com/gb/products/2907753>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2907753>



cUL Recognized
Approval ID: E211944



UL Recognized
Approval ID: E211944



EAC
Approval ID: RU S-DE.BL08.W.00764



UL Listed
Approval ID: E123528



cUL Listed
Approval ID: E123528

DNV

Approval ID: TAA000011F



IECEE CB Scheme
Approval ID: DE/PTZ/0048



NK
Approval ID: TA25015M



UL Recognized
Approval ID: E211944



IECEE CB Scheme
Approval ID: DE/PTZ/0048



cUL Recognized
Approval ID: E211944

QUINT4-S-ORING/12-24DC/1X40/+ - Redundancy module, with protective coating



2907753

<https://www.phoenixcontact.com/gb/products/2907753>



cUL Listed

Approval ID: E123528



UL Listed

Approval ID: E123528

ClassNK

NK

Approval ID: TA25015M

DNV

Approval ID: TAA000011F



EAC Ex

Approval ID: KZ 7500525010102095



IECEx

Approval ID: IECEx SIQ 21.0001X



cUL Listed

Approval ID: E199827



UL Listed

Approval ID: E199827



ATEX

Approval ID: SIQ 21 ATEX 183 X



NEPSI-EX

Approval ID: GYJ21.1004X



UKCA-EX

Approval ID: EXV21UKEX1072X_00

QUINT4-S-ORING/12-24DC/1X40/+ - Redundancy module, with protective coating



2907753

<https://www.phoenixcontact.com/gb/products/2907753>



ATEX

Approval ID: PTB 24 ATEX 2001 X



UL Listed

Approval ID: E199827



cUL Listed

Approval ID: E199827



IECEx

Approval ID: IECEx SIQ 21.0001X



EAC Ex

Approval ID: KZ 7500525010102095



IECEx

Approval ID: IECEx PTB 24.0003X



ATEX

Approval ID: SIQ 21 ATEX 183 X



UKCA-EX

Approval ID: EXV21UKEX1072X_00



NEPSI-EX

Approval ID: GYJ21.1004X



CCC

Approval ID: 2021322303003918



CCC

Approval ID: 2021322303003918

QUINT4-S-ORING/12-24DC/1X40/+ - Redundancy module, with protective coating



2907753

<https://www.phoenixcontact.com/gb/products/2907753>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27371010 |
| ECLASS-15.0 | 27371010 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000683 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 32151500 |
|-------------|----------|

QUINT4-S-ORING/12-24DC/1X40/+ - Redundancy module, with protective coating



2907753

<https://www.phoenixcontact.com/gb/products/2907753>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c), 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-25 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 50e006be-a325-447c-83fd-9bc9751ce8d8 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 11.26 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk