

# PSI-REP-RS485W2 - Repeater



2313096

<https://www.phoenixcontact.com/us/products/2313096>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Modular repeater for electrical isolation and range increase in RS-485 2-wire bus systems up to 500 kbps, 4-way isolation, rail-mountable, supply 24 V DC

## Product description

The performance and availability of bus systems can be significantly increased by using repeaters. In addition to electrical isolation, bus segmentation with repeaters makes it possible to multiply the permissible coverage of the network and to extend the number of devices.

## Your advantages

- Data rates of up to 500 kbps (adjustable via DIP switches)
- High-quality 4-way isolation between all interfaces
- Bit oversampling for reliable detection of sporadic disturbances
- Bit retiming for unrestricted cascading of devices
- Integrated, connectable termination resistors
- Can be combined with PSI-MOS FO converters in a modular way thanks to DIN rail connectors
- Approved for use in zone 2

## Commercial data

Item number	2313096
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN11
Product key	DNC122
GTIN	4046356098816
Weight per piece (including packing)	258 g
Weight per piece (excluding packing)	240.8 g
Customs tariff number	85176200
Country of origin	DE

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

#### Utilization restriction

CCCex note	Use in potentially explosive areas is not permitted in China.
------------	---

### Product properties

Product type	Interface converter
MTTF	1439 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	717 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%)
	305 Years (SN 29500 standard, temperature 40°C, operating cycle 100%)
MTBF	1247 Years (Telcordia standard, 25°C temperature, 21% operating cycle (5 days a week, 8 hours a day))
	261 Years (Telcordia standard, 40°C temperature, 34.25% operating cycle (5 days a week, 12 hours a day))

### Electrical properties

Electrical isolation	VCC // TBUS // RS-485 (A) // RS-485 (B)
Maximum power dissipation for nominal condition	1.8 W
Test voltage data interface/power supply	1.5 kV <sub>rms</sub> (50 Hz, 1 min.)
Test voltage data interfaces	1.5 kV

#### Supply

Supply voltage range	18 V DC ... 30 V DC (via pluggable COMBICON screw terminal block)
Nominal supply voltage	24 V DC
Typical current consumption	75 mA (24 V DC ...)
Max. current consumption	≤ 2 A (For operation in a joining station, via the DIN rail connector)

### Connection data

#### Supply

Stripping length	7.00 mm
Tightening torque	0.6 Nm ... 0.8 Nm

### Interfaces

Bit distortion, input	max. ± 35 %
Bit distortion, output	< 6.25 %
Bit delay	< 1 bit
Signal	Modbus

# PSI-REP-RS485W2 - Repeater




2313096

<https://www.phoenixcontact.com/us/products/2313096>

Transmission channels	2 (1/1), TD, RD, half duplex
Data: RS-485 interface, in acc. with EIA/TIA-485, DIN 66259-4/RS-485 2-wire	
Transmission speed	4.8/9.6/19.2/38.4/57.6/75/93.75/115.2/136/187.5/375/500 kbps (Can be set manually)
Connection method	Pluggable screw connection
Transmission length	≤ 1200 m (depends on transmission speed, bus system and cable type)
Termination resistor	390 Ω (Can be connected to port A and B)
	150 Ω
	390 Ω
Single conductor/terminal point, rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Single-wire/terminal point, flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Max. AWG conductor cross-section, flexible	12
Min. AWG conductor cross-section, flexible	24
Single-wire/terminal point, rigid AWG max.	12
Single-wire/terminal point, rigid AWG min.	24
Transmission medium	2-wire twisted pair, shielded
File format/coding	UART (11/10 bit switchable; NRZ)
Data direction switching	Automatic control, min. station response time 2 bits

## Dimensions

Dimensional drawing	
Width	35 mm
Height	99 mm
Depth	105 mm

## Material specifications

Color (Housing)	gray (RAL 7042)
Material (Housing)	PA 6.6-FR

## Mechanical tests

Free fall in accordance with IEC 60068-2-32	Free fall: 1 m
Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	Operation: 5g, 10...150 Hz, 2.5 h, in XYZ direction
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	Operation: 15g, 11 ms period, half-sine shock pulse

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
----------------------	------

# PSI-REP-RS485W2 - Repeater



2313096

<https://www.phoenixcontact.com/us/products/2313096>

Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 5000 m (For restrictions, see the manufacturer's declaration for altitude operation)
	≤ 2000 m (Hazardous locations)
Permissible humidity (operation)	10 % ... 95 % (non-condensing)

## Approvals

### CE

Certificate	CE-compliant
-------------	--------------

### ATEX

Identification	⊕ II 3 G Ex ec IIC T5 Gc
Certificate	UL 21 ATEX 2550X
Note	Please follow the special installation instructions in the documentation!

### IECEX

Identification	Ex ec IIC T5 Gc
Certificate	IECEX ULD 21.0013X

### UL, USA/Canada

Identification	Class I, Zone 2, AEx ec IIC T5 Gc
	Ex ec IIC T5 Gc X
	Class I, Div. 2, Groups A, B, C, D

### Corrosive gas test

Identification	ISA-S71.04-1985 G3 Harsh Group A
----------------	----------------------------------

## EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise immunity	EN 61000-4-2

### Noise emission

Standards/regulations	EN 55011
-----------------------	----------

### Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

### Electrostatic discharge

Contact discharge	± 6 kV
Discharge in air	± 8 kV
Comments	Criterion B

### Electromagnetic HF field

Standards/regulations	EN 61000-4-3
-----------------------	--------------

### Electromagnetic HF field

# PSI-REP-RS485W2 - Repeater



2313096

<https://www.phoenixcontact.com/us/products/2313096>

Frequency range	80 MHz ... 3 GHz
Field intensity	10 V/m
Comments	Criterion A

## Fast transients (burst)

Standards/regulations	EN 61000-4-4
-----------------------	--------------

## Fast transients (burst)

Input	± 2 kV
Signal	± 2 kV
Comments	Criterion B

## Surge current load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

## Surge current load (surge)

Input	± 0.5 kV
Signal	± 1 kV
Comments	Criterion B

## Conducted interference

Standards/regulations	EN 61000-4-6
-----------------------	--------------

## Conducted interference

Comments	Criterion A
Voltage	10 V

## Emitted interference

Standards/regulations	EN 55011
Comments	Class A, industrial applications

## Criteria

Criterion A	Normal operating behavior within the specified limits.
Criterion B	Temporary impairment to operational behavior that is corrected by the device itself.

## Standards and regulations

Free from substances that could impair the application of coating	VDMA 24364:2018-05
Standards/regulations	EN 62368

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# PSI-REP-RS485W2 - Repeater




2313096

<https://www.phoenixcontact.com/us/products/2313096>

## Drawings

Dimensional drawing



Housing dimensions


# PSI-REP-RS485W2 - Repeater

2313096

<https://www.phoenixcontact.com/us/products/2313096>




Application drawing



Branch/bus segmentation

Application drawing



Line structure


# PSI-REP-RS485W2 - Repeater

2313096

<https://www.phoenixcontact.com/us/products/2313096>



Application drawing



Star structure


# PSI-REP-RS485W2 - Repeater

2313096

<https://www.phoenixcontact.com/us/products/2313096>



Application drawing



Tree structure


# PSI-REP-RS485W2 - Repeater

2313096

<https://www.phoenixcontact.com/us/products/2313096>



Schematic diagram




Front view

# PSI-REP-RS485W2 - Repeater

2313096

<https://www.phoenixcontact.com/us/products/2313096>

## Schematic diagram



DIP switches


# PSI-REP-RS485W2 - Repeater

2313096

<https://www.phoenixcontact.com/us/products/2313096>




Schematic diagram



Connecting the cables

Schematic diagram




Connecting the cables

# PSI-REP-RS485W2 - Repeater



2313096

<https://www.phoenixcontact.com/us/products/2313096>



Basic circuit diagram

# PSI-REP-RS485W2 - Repeater



2313096

<https://www.phoenixcontact.com/us/products/2313096>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2313096>



**cULus Listed**

Approval ID: E238705



**cULus Recognized**

Approval ID: E238705



**cUL Listed**

Approval ID: E199827



**UL Listed**

Approval ID: E199827



**IECEx**

Approval ID: IECEx ULD 21.0013X



**ATEX**

Approval ID: UL 21 ATEX 2550X

# PSI-REP-RS485W2 - Repeater



2313096

<https://www.phoenixcontact.com/us/products/2313096>

## Classifications

### ECLASS

ECLASS-13.0	27242208
ECLASS-15.0	27242208

### UNSPSC

UNSPSC 21.0	43222600
-------------	----------

# PSI-REP-RS485W2 - Repeater



2313096

<https://www.phoenixcontact.com/us/products/2313096>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	9ae6a00b-07c9-4c16-a83d-d5932c6a7119

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)