

PP-RJ-IDC-F - Patch panel



2703023

<https://www.phoenixcontact.com/us/products/2703023>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Patch panel, RJ45 jack on IDC terminal blocks, CAT5e, 10/100/1000 Mbps, DIN rail adapter, IP20, shield contacting with strain relief, shield current monitoring, surge protection

Product description

Ethernet patch panels enable quick and easy connection between the field cabling and control cabinet cabling. The passive termination panels are a convenient alternative to the on-site assembly of RJ45 connectors. The IDC fast connection terminal blocks enable tool-free connection without stripping the single-core wires. The terminal blocks with inserted wires are simply pressed shut by hand. Observe the permissible single-core wire diameter and the permissible insulation material.

Your advantages

- 10/100/1000 Mbps
- Extended temperature range of -40 °C ... +75 °C
- Fast connection of the field cable
- Wiring space covered with front panel cover
- Tool-free shield contacting with strain relief
- Integrated surge protection to ensure high system availability
- Shield current monitoring with visual display
- Shipbuilding approval in accordance with DNV GL
- PoE-capable in accordance with IEEE 802.3bt, type 4

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2703023 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN07 |
| Product key | DNC334 |
| GTIN | 4055626463353 |
| Weight per piece (including packing) | 142.7 g |
| Weight per piece (excluding packing) | 124.2 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

PP-RJ-IDC-F - Patch panel



2703023

<https://www.phoenixcontact.com/us/products/2703023>

Technical data

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Utilization restriction

| | |
|------------|---|
| CCCex note | Use in potentially explosive areas is not permitted in China. |
|------------|---|

Product properties

| | |
|-------------------------|--|
| Product type | Patch panel |
| IEC test classification | C2 |
| MTTF | 3281 Years (SN 29500 standard, temperature 25°C, operating cycle 21%) |
| | 1245 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%) |
| | 472 Years (SN 29500 standard, temperature 40°C, operating cycle 100%) |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Pollution degree | 2 |

Electrical properties

| | |
|---|----------------|
| Electrical isolation | FE // Ethernet |
| Maximum power dissipation for nominal condition | 0 W |
| Rated insulation voltage | 85 V DC |

Supply

| | |
|----------------------|--|
| Supply voltage range | 36 V DC ... 52 V DC ± 10 % (via PoE) |
| | 42 V DC ... 57 V DC (in acc. with UL) |

Function

| | |
|---------------------|------------------------------------|
| Designation | Shield current monitoring |
| Switch-on threshold | ≥ 30 mA |
| Local diagnostics | Yellow LED |
| Precision | ± 5 % |
| Response time | 3 s |
| Current | ≤ 1.5 A |
| Power consumption | 270 mW (Shield current monitoring) |
| Impedance | ≤ 1 Ω |
| Voltage | ≤ 10 V |

Interfaces

Data: Ethernet interface, 10/100/1000Base-T(X) in accordance with IEEE 802.3

PP-RJ-IDC-F - Patch panel

2703023

<https://www.phoenixcontact.com/us/products/2703023>

| | |
|---|---|
| Serial transmission speed | 10/100/1000 Mbps |
| Frequency range | 125 MHz |
| Connection method | IDC connection |
| Note on the connection method | CAT5e |
| Pin assignment | 1:1 |
| Transmission length | 100 m (including patch cables) |
| Single conductor/terminal point, rigid | 0.14 mm ² ... 0.34 mm ² |
| Single-wire/terminal point, flexible | 0.14 mm ² ... 0.34 mm ² |
| Max. AWG conductor cross-section, flexible | 22 |
| Min. AWG conductor cross-section, flexible | 26 |
| Single-wire/terminal point, rigid AWG max. | 22 |
| Single-wire/terminal point, rigid AWG min. | 26 |
| Wire diameter incl. insulation | 1.6 mm (Terminal block is tested with PVC insulation - other insulation materials available on request) |
| Frequency of connections between conductors of the same cross section | 10 |
| Transmission medium | Copper |
| Maximum output power | 60 W |
| Maximum output current | 725 mA (PoE) |
| Current carrying capacity | ≤ 1.5 A (≤ 60 W (PoE+)) |


Data: Ethernet interface, 10/100/1000Base-T(X) in accordance with IEEE 802.3

| | |
|-------------------|-----------|
| Connection method | RJ45 jack |
|-------------------|-----------|

Signaling

| | |
|------------------------|------------|
| Optical representation | Yellow LED |
|------------------------|------------|

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 23.8 mm |
| Height | 101.3 mm |
| Depth | 86 mm |

Material specifications

| | |
|--|-----------------------|
| Color (Housing) | light gray (RAL 7035) |
| Material (Housing) | Plastic |
| Flammability rating according to UL 94 | V0 |

Cable/line

| | |
|-------------------------|-------------------|
| External cable diameter | 5.5 mm ... 6.5 mm |
|-------------------------|-------------------|

Mechanical tests

| | |
|--|--|
| Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6 | Operation: 10 Hz ... 57 Hz, amplitude ± 3.5 mm, 57 Hz ... 150 Hz, 5g |
| Shock in accordance with EN 60068-2-27/IEC 60068-2-27 | Operation: 30g for 11 ms, three shocks in each spatial direction |
| Continuous shock in accordance with EN 60068-2-27/IEC 60068-2-27 | Operation: 10g for 16 ms, 1000 shocks in each spatial direction |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Degree of protection | IP20 (Manufacturer's declaration) |
| Ambient temperature (operation) | -40 °C ... 75 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Altitude | ≤ 5000 m (For restrictions, see the manufacturer's declaration for altitude operation) |
| | ≤ 2000 m (Restrictions for ATEX applications) |
| Permissible humidity (operation) | 10 % ... 95 % (non-condensing) |

Approvals

CE

| | |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

ATEX

| | |
|----------------|---|
| Identification | Ⓜ II 3 G Ex ec nC IIC T4 Gc |
| Certificate | PxCIF18ATEX2703020X |
| Note | Please follow the special installation instructions in the documentation! |

UL, USA/Canada

| | |
|----------------|---|
| Identification | Class I, Zone 2, AEx nA IIC T4, Ex nA IIC Gc X T4 |
| | Class I, Div. 2, Groups A, B, C, D |

UL, USA

| | |
|-------------|--------------------------------------|
| Certificate | UL 60079-0 Ed. 6 / UL 60079-15 Ed. 4 |
|-------------|--------------------------------------|

UL, Canada

| | |
|-------------|---|
| Certificate | CSA 22.2 No. 60079-0 Ed. 3 / CSA 22.2 No. 60079-15:16 |
|-------------|---|

Corrosive gas test

| | |
|----------------|----------------------------------|
| Identification | ISA-S71.04-1985 G3 Harsh Group A |
|----------------|----------------------------------|

Shipbuilding

| | |
|----------------|--------|
| Identification | DNV GL |
|----------------|--------|

Shipbuilding data

| | |
|-------------|---|
| Temperature | D |
| Humidity | B |
| Vibration | B |

PP-RJ-IDC-F - Patch panel



2703023

<https://www.phoenixcontact.com/us/products/2703023>

| | |
|-----|---|
| EMC | B |
|-----|---|

EMC data

| | |
|-------------------------------|---|
| Electromagnetic compatibility | Conformance with EMC Directive 2014/30/EU |
| | FCC Part 15B Class A |
| | CISPR 22 |

Electrostatic discharge

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-2 |
|-----------------------|--------------|

Electrostatic discharge

| | |
|--------------------|-----------------------|
| Contact discharge | ± 6 kV (Test Level 3) |
| Discharge in air | ± 8 kV (Test Level 3) |
| Indirect discharge | ± 6 kV |
| Comments | Criterion B |

Electromagnetic HF field

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-3 |
|-----------------------|--------------|

Electromagnetic HF field

| | |
|-----------------|---------------------------------|
| Frequency range | 80 MHz ... 3 GHz (Test Level 3) |
| Field intensity | 10 V/m |
| Comments | Criterion A |

Fast transients (burst)

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-4 |
|-----------------------|--------------|

Fast transients (burst)

| | |
|----------|---------------------|
| Input | ± 2.2 kV (1 minute) |
| Signal | ± 2.2 kV (1 minute) |
| Comments | Criterion B |

Surge current load (surge)

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-5 |
|-----------------------|--------------|

Surge current load (surge)

| | |
|--------|----------------------------------|
| Input | ± 0.5 kV |
| Signal | ± 1 kV (Data line, asymmetrical) |

Conducted interference

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-6 |
|-----------------------|--------------|

Conducted interference

| | |
|-----------------|---------------------|
| Frequency range | 0.15 MHz ... 80 MHz |
| Comments | Criterion A |
| Voltage | 10 V |

Emitted interference

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-6-4 |
|-----------------------|--------------|

PP-RJ-IDC-F - Patch panel



2703023

<https://www.phoenixcontact.com/us/products/2703023>

| | |
|----------|----------------------------------|
| Comments | Class A, industrial applications |
|----------|----------------------------------|

Emitted interference

| | |
|-----------------------|--|
| Standards/regulations | EN 61000-6-3 |
| Comments | Class B, domain of use: residential and small commercial |

Criteria

| | |
|-------------|--|
| Criterion A | Normal operating behavior within the specified limits. |
| Criterion B | Temporary impairment to operational behavior that is corrected by the device itself. |

Standards and regulations

| | |
|-----------------------|---|
| Standards/regulations | DIN EN 61643-21 |
| Standard designation | Surge protective devices in the low-voltage range, in telecommunications and signaling networks |

Mounting

| | |
|-----------------------|--|
| Mounting type | DIN rail mounting |
| Assembly note | The product can be snapped onto all 35 mm DIN rails in accordance with EN/IEC 60715. |
| Useable DIN rail type | DIN rail: 35 mm |

PP-RJ-IDC-F - Patch panel


2703023

<https://www.phoenixcontact.com/us/products/2703023>



Drawings

Dimensional drawing



Housing dimensions


PP-RJ-IDC-F - Patch panel

2703023

<https://www.phoenixcontact.com/us/products/2703023>



Schematic diagram



Front view



PP-RJ-IDC-F - Patch panel

2703023

<https://www.phoenixcontact.com/us/products/2703023>





Schematic diagram



Mounting on a DIN rail

Schematic diagram



Removal


PP-RJ-IDC-F - Patch panel

2703023

<https://www.phoenixcontact.com/us/products/2703023>



Schematic diagram



Open shield contact spring


PP-RJ-IDC-F - Patch panel

2703023

<https://www.phoenixcontact.com/us/products/2703023>



Schematic diagram



Inserting the cable


PP-RJ-IDC-F - Patch panel

2703023

<https://www.phoenixcontact.com/us/products/2703023>



Schematic diagram




Close shield contact spring

PP-RJ-IDC-F - Patch panel

2703023


<https://www.phoenixcontact.com/us/products/2703023>

Schematic diagram



Shield current monitoring

Schematic diagram



Stripping length


PP-RJ-IDC-F - Patch panel

2703023

<https://www.phoenixcontact.com/us/products/2703023>



Circuit diagram



Circuit diagram

PP-RJ-IDC-F - Patch panel

2703023

<https://www.phoenixcontact.com/us/products/2703023>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2703023>



cULus Listed

Approval ID: E238705



DNV GL

Approval ID: TAA00001KR

PP-RJ-IDC-F - Patch panel



2703023

<https://www.phoenixcontact.com/us/products/2703023>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19170112 |
| ECLASS-15.0 | 19170112 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001128 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43223300 |
|-------------|----------|

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | b4311499-a599-4817-84c1-5e65ffb15e57 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 8.216 kg CO2e |
|---------|---------------|