

# PSM-ME-RS232/RS485-P - Interface converter



2744416

<https://www.phoenixcontact.com/us/products/2744416>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Interface converter, for converting RS-232 (V.24) to RS-422 (V.11) and RS-485, with electrical isolation, 2 channels, rail-mountable

## Product description

The RS-485 standard allows more than two devices to communicate with one another. Converting the V.24 (RS-232) point-to-point interface into the bus-capable RS-485 standard makes it possible to network up to 32 devices via a 2- or 4-wire cable.

## Your advantages

- Mounting on standard EN DIN rails
- Transmission speed of 4.8 Kbps ... 115.2 Kbps
- High-quality 3-way isolation between power supply, RS-232, and RS-422/RS-485 for safe decoupling of potentials with 2 kV
- RS-422 4-wire point-to-point operation
- RS-485 2-wire operation, half duplex
- RS-485 4-wire operation, full duplex
- Automatic RS-485 transmit/receive changeover
- Integrated data indicator for dynamic indication of transmit and receive data
- Integrated surge protection with transient discharge to the DIN rail
- Shipbuilding approval in accordance with DNV GL



## Commercial data

|                        |         |
|------------------------|---------|
| Item number            | 2744416 |
| Packing unit           | 1 pc    |
| Minimum order quantity | 1 pc    |
| Sales key              | DN11    |
| Product key            | DNC111  |

# PSM-ME-RS232/RS485-P - Interface converter



2744416

<https://www.phoenixcontact.com/us/products/2744416>

|                                      |               |
|--------------------------------------|---------------|
| GTIN                                 | 4017918171780 |
| Weight per piece (including packing) | 207.3 g       |
| Weight per piece (excluding packing) | 196.1 g       |
| Customs tariff number                | 85176200      |
| Country of origin                    | DE            |

## Technical data

### Notes

#### Note on application

|                     |                         |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

#### Utilization restriction

|            |   |
|------------|---|
| CCCex note | Use in potentially explosive areas is not permitted in China. |
|------------|---|

### Product properties

|              |   |
|--------------|---|
| Product type | Interface converter   |
| Application  | RS-232  |
|              | RS-422  |
|              | RS-485  |
| MTTF         | 1654 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)                                   |
|              | 746 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%)                                 |
|              | 310 Years (SN 29500 standard, temperature 40°C, operating cycle 100%)                                   |
| MTBF         | 10 Years (Telcordia standard, temperature 40 °C, operating cycle 100 % (7 days a week, 24 hours a day)) |

#### Insulation characteristics

|                  |   |
|------------------|---|
| Pollution degree | 2 |
|------------------|---|

### Electrical properties

|   |                                |
|---|--------------------------------|
| Electrical isolation                            | VCC // V.24 (RS-232) // RS-485 |
| Maximum power dissipation for nominal condition | 2.04 W                         |
| Test voltage data interface/power supply        | 1.5 kV AC                      |
|   | 1.5 kV AC                      |
| Test voltage data interfaces                    | 1.5 kV AC                      |

#### Supply

|                             |   |
|-----------------------------|---|
| Supply voltage range        | 19.2 V AC/DC ... 28.8 V AC/DC (via pluggable COMBICON screw terminal block) |
| Nominal supply voltage      | 24 V AC/DC ±20 %  |
| Typical current consumption | 25 mA (24 V DC)   |

### Connection data

#### Supply

|   |   |
|---|---|
| Single conductor/terminal point, rigid  | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Single-wire/terminal point, flexible    | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section, flexible [AWG] | 24 ... 12                                   |
| Stripping length                        | 7.00 mm                                     |

# PSM-ME-RS232/RS485-P - Interface converter



2744416

<https://www.phoenixcontact.com/us/products/2744416>

|                   |                     |
|-------------------|---------------------|
| Tightening torque | 0.56 Nm ... 0.79 Nm |
|-------------------|---------------------|

## Interfaces

|                       |                                |
|-----------------------|--------------------------------|
| Interface             | RS-232/-485                    |
| Bit distortion        | ≤ 5 %                          |
| Bit delay             | ≤ 2.5 μs                       |
| Signal                | Modbus                         |
| Transmission channels | 2 (1/1), RxD, TxD, full duplex |

Data: V.24 (RS-232) interface in acc. with ITU-T V.28, EIA/TIA-232, DIN 66259-1

|  |   |
|--|---|
| Serial transmission speed                  | 1.2; 2.4; 4.8; 7.2; 9.6; 19.2; 31.25; 38.4; 57.6; 75; 93.75; 115.2 kbps |
| Connection method                          | D-SUB 9 plug  |
| Pin assignment                             | DTE/DCE switchover via switch   |
| Transmission length                        | 15 m (shielded twisted pair)  |
| Single conductor/terminal point, rigid     | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                             |
| Single-wire/terminal point, flexible       | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                             |
| Max. AWG conductor cross-section, flexible | 12  |
| Min. AWG conductor cross-section, flexible | 24  |
| Protocols supported                        | transparent protocol  |

Data: RS-422 interface in acc. with ITU-T V.11, EIA/TIA-422, DIN 66348-1

|  |   |
|--|---|
| Serial transmission speed                  | 1.2; 2.4; 4.8; 9.6; 19.2; 38.4; 57.6; 75; 93.75; 115.2 kbps |
| Connection method                          | Pluggable screw connection                                  |
| Tightening torque                          | 0.5 Nm ... 0.6 Nm (Shield clamp)                            |
| Transmission length                        | 1200 m (shielded twisted pair)                              |
| Termination resistor                       | 390 Ω<br>150 Ω<br>390 Ω (Can be connected)                  |
| Single-wire/terminal point, flexible       | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                 |
| Max. AWG conductor cross-section, flexible | 13  |
| Min. AWG conductor cross-section, flexible | 24  |
| Stripping length                           | 7 mm  |
| Protocols supported                        | transparent protocol  |

Data: RS-485 interface in acc. with EIA/TIA-485, DIN 66259-1

|  |   |
|--|---|
| Serial transmission speed                  | 1.2; 2.4; 4.8; 9.6; 19.2; 38.4; 57.6; 75; 93.75; 115.2 kbps |
| Connection method                          | Pluggable screw connection                                  |
| Transmission length                        | 1200 m (shielded twisted pair)                              |
| Termination resistor                       | 390 Ω<br>150 Ω<br>390 Ω (Can be connected)                  |
| Single-wire/terminal point, flexible       | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                 |
| Max. AWG conductor cross-section, flexible | 14  |
| Min. AWG conductor cross-section, flexible | 24  |
| Data direction switching                   | Automatic control or via RTS/CTS                            |

# PSM-ME-RS232/RS485-P - Interface converter




2744416

<https://www.phoenixcontact.com/us/products/2744416>

|                     |                      |
|---------------------|----------------------|
| Protocols supported | transparent protocol |
|---------------------|----------------------|

## Dimensions

|                     |  |
|---------------------|--|
| Dimensional drawing |  |
| Width               | 22.5 mm  |
| Height              | 99 mm  |
| Depth               | 114.5 mm   |

## Material specifications

|                    |                  |
|--------------------|------------------|
| Color (Housing)    | green (RAL 6021) |
| Material (Housing) | PA 6.6-FR        |

## Mechanical tests

|  |   |
|--|---|
| Free fall in accordance with IEC 60068-2-32                        | Free fall: 1 m  |
| Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6 | Vibration (operation): 5g, 10...150 Hz, 2.5 h, in XYZ direction |
| Shock in accordance with EN 60068-2-27/IEC 60068-2-27              | Shock (operation): 25g, 11 ms period, half-sine shock pulse     |

## Environmental and real-life conditions

### Ambient conditions

|   |  |
|---|--|
| Degree of protection                    | IP20   |
| Ambient temperature (operation)         | -40 °C ... 70 °C   |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C   |
| Altitude                                | ≤ 5000 m (For restrictions, see the manufacturer's declaration for altitude operation) |
| Permissible humidity (operation)        | 10 % ... 95 % (non-condensing)   |

## Approvals

### CE

|             |              |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

### ATEX

|                |   |
|----------------|---|
| Identification | ⊕ II 3 G Ex ec IIC T4 Gc  |
| Certificate    | IBExU16ATEXB004 X   |
| Note           | Please follow the special installation instructions in the documentation! |

### IECEX

|                |                    |
|----------------|--------------------|
| Identification | Ex ec IIC T4 Gc    |
| Certificate    | IECEX IBE 15.0034X |

# PSM-ME-RS232/RS485-P - Interface converter



2744416

<https://www.phoenixcontact.com/us/products/2744416>

## UL, USA/Canada

|                |                                       |
|----------------|---------------------------------------|
| Identification | 508 Recognized                        |
|                | Class I, Zone 2, AEx nA IIC T4        |
|                | Ex nA IIC T4 Gc X                     |
|                | Class I, Div. 2, Groups A, B, C, D T4 |

## KC approval for South Korea

|             |                        |
|-------------|------------------------|
| Certificate | MSIP-REI-PCK-ME2744416 |
|-------------|------------------------|

## Corrosive gas test

|                |                                  |
|----------------|----------------------------------|
| Identification | ISA-S71.04-1985 G3 Harsh Group A |
|----------------|----------------------------------|

## Shipbuilding

|                |        |
|----------------|--------|
| Identification | DNV GL |
|----------------|--------|

## Shipbuilding data

|             |   |
|-------------|---|
| Temperature | B   |
| Humidity    | A   |
| Vibration   | A   |
| EMC         | B   |
| Enclosure   | Required protection according to the Rules shall be provided upon installation on board |

## EMC data

|                               |   |
|-------------------------------|---|
| Electromagnetic compatibility | Conformance with EMC Directive 2014/30/EU |
| Noise immunity                | EN 61000-6-2:2005                         |

## Noise emission

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-6-4 |
|-----------------------|--------------|

## Electrostatic discharge

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-2 |
|-----------------------|--------------|

## Electrostatic discharge

|                   |                       |
|-------------------|-----------------------|
| Contact discharge | ± 6 kV (Test Level 3) |
| Discharge in air  | ± 8 kV (Test Level 3) |
| Comments          | Criterion B           |

## Electromagnetic HF field

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-3 |
|-----------------------|--------------|

## Electromagnetic HF field

|                 |                                 |
|-----------------|---------------------------------|
| Frequency range | 26 MHz ... 3 GHz (Test Level 3) |
| Field intensity | 10 V/m                          |
| Comments        | Criterion A                     |

## Fast transients (burst)

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-4 |
|-----------------------|--------------|

# PSM-ME-RS232/RS485-P - Interface converter



2744416

<https://www.phoenixcontact.com/us/products/2744416>

## Fast transients (burst)

|          |                         |
|----------|-------------------------|
| Input    | ± 2.2 kV (Test Level 3) |
| Signal   | ± 2.2 kV (Test Level 3) |
| Comments | Criterion B             |

## Surge current load (surge)

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-5 |
|-----------------------|--------------|

## Surge current load (surge)

|          |                                  |
|----------|----------------------------------|
| Input    | ± 0.5 kV (DC supply)             |
| Signal   | ± 1 kV (Data line, asymmetrical) |
| Comments | Criterion B                      |

## Conducted interference

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-4-6 |
|-----------------------|--------------|

## Conducted interference

|                 |                     |
|-----------------|---------------------|
| Frequency range | 0.15 MHz ... 80 MHz |
| Comments        | Criterion A         |
| Voltage         | 10 V                |

## Emitted interference

|                       |                                  |
|-----------------------|----------------------------------|
| Standards/regulations | EN 55011                         |
| Comments              | Class A, industrial applications |

## Criteria

|             |  |
|-------------|--|
| Criterion A | Normal operating behavior within the specified limits.                               |
| Criterion B | Temporary impairment to operational behavior that is corrected by the device itself. |

## Mounting

|               |                   |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

# PSM-ME-RS232/RS485-P - Interface converter


2744416

<https://www.phoenixcontact.com/us/products/2744416>




## Drawings

Dimensional drawing




Slim design

Application drawing




Remote transmission

Application drawing




Interface adaptation or programming connection

Application drawing



Controller interface

Application drawing




Networking of RS-232 devices

# PSM-ME-RS232/RS485-P - Interface converter

2744416

<https://www.phoenixcontact.com/us/products/2744416>


Application drawing



 = Switch on bus terminating resistor

Activate termination resistors - RS-485

Application drawing




 = Switch on bus terminating resistor

Activate termination resistors - RS-422

2744416


<https://www.phoenixcontact.com/us/products/2744416>

Connection diagram



RS-422/RS-485 4-wire

Connection diagram



RS-485 interface


# PSM-ME-RS232/RS485-P - Interface converter



2744416

<https://www.phoenixcontact.com/us/products/2744416>

Schematic diagram



Removal


# PSM-ME-RS232/RS485-P - Interface converter



2744416


<https://www.phoenixcontact.com/us/products/2744416>

Schematic diagram



DIP switches

Circuit diagram



Basic circuit diagram

# PSM-ME-RS232/RS485-P - Interface converter



2744416

<https://www.phoenixcontact.com/us/products/2744416>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2744416>



**cUL Recognized**  
Approval ID: E238705



**UL Recognized**  
Approval ID: E238705



**DNV GL**  
Approval ID: TAA00001KR



**KC**  
Approval ID: MSIP-REI-PCK-ME27444



**cUL Recognized**  
Approval ID: E199827

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 24 V                  | 0.085 A               | -                 | -                           |



**cUL Listed**  
Approval ID: E199827



**UL Listed**  
Approval ID: E199827

# PSM-ME-RS232/RS485-P - Interface converter



2744416

<https://www.phoenixcontact.com/us/products/2744416>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27242208 |
| ECLASS-15.0 | 27242208 |

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 32151700 |
|-------------|----------|

2744416

<https://www.phoenixcontact.com/us/products/2744416>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes                |
| Exemption                               | 6(c), 7(a), 7(c)-I |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 0975dfe5-6e5e-4de1-b8e2-f94de5c2b5d6 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)